


## SmartRack 6U Vertical Wall-Mount Rack Bracket

MODEL NUMBER: SRWALLBRKT6U



6U wall-mount bracket allows vertical installation of a 6U rack-mount device up to 200 lb.

### Description

The SRWALLBRKT6U SmartRack® 6U Vertical Wall-Mount Rack Bracket is recommended for home offices and small businesses with rack-mount equipment that doesn't need to be secured and no room on the premises for a standard 19-inch server rack.

Made from heavy-duty cold-rolled steel with a durable black powder-coated finish, this 6U wall-mount bracket easily attaches to the wall of your back office or closet with user-supplied hardware. Wall-mounting holes are spaced 16 inches part to match standard wall-stud placement. Or you can install the bracket horizontally beneath a desk or workbench for instant access.

Use the included hardware to attach your 6U rack-mount equipment, such as a network switch or UPS system, to the steel bracket's rails. Its maximum load capacity is 200 lbs (90.7 kgs). Connected equipment hangs flush against the wall, allowing you unrestricted access. The SRWALLBRKT6U is compatible with most EIA-standard 19-inch two-post rack equipment.

### Features

#### 6U Wall-Mount Bracket Allows Vertical Mounting in a Closet or Back Office

- Recommended for home offices and small businesses with no room for standard 19 in. rack
- Provides open, unrestricted access to equipment and cabling
- Maximum load capacity of 200 lbs (90.7 kgs)
- Cold-rolled steel construction with black powder-coated finish designed for long life
- Ships fully assembled for quick installation

#### Attaches to the Wall with User-Supplied Hardware

- Wall-mounting holes spaced 16 in. apart for standard wall stud placement
- Also mounts horizontally beneath a desk or workbench
- Component hangs flush against the wall for unrestricted out-of-the-way access

#### Compatible with EIA-Standard 19 in. 2-Post Rack Equipment

- Hardware included for mounting 6U rack equipment
- Rails support square-hole mounting

## Specifications

### Highlights

- 19-inch wall-mount rack with maximum load capacity of 200 lbs (90.7 kgs)
- Provides open, unrestricted access to equipment and cabling
- Made from cold-rolled steel with black powder-coated finish
- Equipment-mounting hardware included
- Compatible with most EIA-standard 19 in. 2-post rack equipment

### Package Includes

- SRWALLBRKT6U SmartRack 6U Vertical Wall-Mount Rack Bracket
- (12) M6 screws
- (12) M6 cup washers
- (12) M6 cage nuts
- Installation guide



Powering Business Worldwide

TRIPP LITE  
SERIES

| OVERVIEW                            |                             |
|-------------------------------------|-----------------------------|
| UPC Code                            | 037332203212                |
| Device Compatibility                | Network Switch; Patch Panel |
| Rack Type                           | Bracket                     |
| PHYSICAL                            |                             |
| Color                               | Black                       |
| Rack Height                         | 6U                          |
| Rack Depth                          | Shallow                     |
| Maximum Device Depth (cm)           | 121.92                      |
| Maximum Device Depth (in.)          | 48                          |
| Maximum Device Depth (mm)           | 1,219                       |
| Maximum Weight Capacity (lbs.)      | 200                         |
| Maximum Weight Capacity (kg)        | 91                          |
| Shipping Dimensions (hwd / in.)     | 10.83 x 21.85 x 18.31       |
| Shipping Dimensions (hwd / cm)      | 27.51 x 55.50 x 46.51       |
| Shipping Weight (lbs.)              | 12.12                       |
| Shipping Weight (kg)                | 5.50                        |
| Unit Dimensions (hwd / in.)         | 11.150 x 19.690 x 11.150    |
| Unit Dimensions (hwd / cm)          | 28.32 x 50.01 x 28.32       |
| Unit Weight (lbs.)                  | 8.38                        |
| Unit Weight (kg)                    | 3.80                        |
| Weight Capacity - Stationary (kg)   | 91                          |
| Weight Capacity - Stationary (lbs.) | 200                         |
| Number of Vertical Mounting Rails   | 2                           |
| FEATURES & SPECIFICATIONS           |                             |
| Built-in Cable Management           | No                          |
| Extra Wide                          | No                          |
| Pre-Installed Casters               | No                          |
| STANDARDS & COMPLIANCE              |                             |
| Product Compliance                  | RoHS; EIA/ECA-310-E         |
| WARRANTY & SUPPORT                  |                             |
| Product Warranty Period (Worldwide) | 5-year limited warranty     |



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.