




Part Number : [2042200202](#)
Product Description : Squba Sealed Receptacle
Assembly, 1.80mm Pitch, Single Row, 2 Circuits,
Natural
Series Number : 204220
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

- [2042200202 sd.pdf](#)
- [2042200000-PK-000.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

Specifications

- [2042200000-AS-000.pdf](#)
- [2042200000-PS-000.pdf](#)
- [2042200000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Dodecamethylcyclohexasiloxane; Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	204220
Description	Squba Sealed Receptacle Assembly, 1.80mm Pitch, Single Row, 2 Circuits, Natural
Application	Power, Signal, Wire-to-Wire
Keyword	Squba 1.8
Product Name	Squba
UPC	196823664373

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	2
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No

Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	2.635/g
Number of Rows	1
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	1.80mm
Pitch - Termination Interface	1.80mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Squba Sealed Plug Assembly, 1.80mm Pitch, Single Row, 2 Circuits, Natural	<u>2042232202</u>
Squba Sealed Plug Assembly with Clipslot, 1.80mm Pitch, Single Row, 2 Circuits, Natural	<u>2042233202</u>

Use with Part(s)

Description	Part Number
Squba 1.8 Receptacle Terminal, Matte Tin Plating, 24-22 AWG	<u>2043010001</u>
Squba 1.8 Receptacle Terminal, Matte Tin Plating, 26 AWG	<u>2043010002</u>

This document was generated on May 13, 2026