



**Part Number :** [1301410027](#)

**Product Description :** Super-Safeway Ground Fault Monitoring Connector 2 Pole/3 Wire, NEMA 5-20, 125V

**Series Number :** 130141

**Status :** Active

**Product Category :** Wiring Devices

**Engineering Part Number :** 1533GCM



---

## Documents and Resources

---

### Product Environment Compliance

#### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

#### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

## Part Details

### General

Status	Active
Category	Wiring Devices
Series	130141
Description	Super-Safeway Ground Fault Monitoring Connector 2 Pole/3 Wire, NEMA 5-20, 125V
IP Rating	N/A
NEMA Configuration	NEMA 5-20
Product Name	Super-Safeway
Specialty	Monitoring
Type	Connector
UPC	78678805849

### Agency

CSA	LR6837
UL	E10176

### Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	125V

### Physical

Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Female
Length	N/A
Lighted Connector	Yes
Locking Blade	No
Net Weight	48.250/g

Poles	2-pole/3-wire
Receptacle Type	Single

---

This document was generated on May 20, 2026