


UMK- C64M-VS - Termination board

2970057

<https://www.phoenixcontact.com/us/products/2970057>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, for IEC 603/DIN 41612 connector, type C, 64-pos., a, c components mounted, with male connector, cable housing with screw interlock

Commercial data

Item number	2970057
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C429
Product key	DK2187
GTIN	4017918087579
Weight per piece (including packing)	312 g
Weight per piece (excluding packing)	298 g
Customs tariff number	85369010
Country of origin	DE

UMK- C64M-VS - Termination board



2970057

<https://www.phoenixcontact.com/us/products/2970057>

Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE
Number of positions	64
Operating mode	100% operating factor

Insulation characteristics

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Electrical properties

Max. permissible operating voltage	125 V AC/DC
Max. permissible current	observe derating
Rated insulation voltage	125 V
Rated surge voltage	1.5 kV

Connection data

Field level

Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross section rigid	0.2 mm ² ... 4 mm ²
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section AWG	24 ... 12

Controller level

Connection method	IEC 603/DIN 41612 connection
Number of connections	1
Number of positions	64

Signaling

Status display present	no
------------------------	----

Dimensions

Item dimensions

Width	134.8 mm
Height	77 mm
Depth	60.27 mm

Material specifications

UMK- C64M-VS - Termination board



2970057

<https://www.phoenixcontact.com/us/products/2970057>

Color	green (RAL 6021)
Housing insulation material	Polyamide PA non-reinforced

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	≤ 2000 m

Standards and regulations

Standards/regulations	EN 60664-1
-----------------------	------------

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

Notes

Notes on operation	Basic insulation is maintained against adjacent modules (in the DIN rail direction).
Notes on operation	Ensure that the supply voltage of the device has a common reference potential.
Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

UMK- C64M-VS - Termination board


2970057

<https://www.phoenixcontact.com/us/products/2970057>



Drawings

Diagram



Derating diagram

UMK- C64M-VS - Termination board

2970057

<https://www.phoenixcontact.com/us/products/2970057>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2970057>



EAC

Approval ID: RU*DE.*09.B.00387/20

UMK- C64M-VS - Termination board



2970057

<https://www.phoenixcontact.com/us/products/2970057>

Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UMK- C64M-VS - Termination board



2970057
<https://www.phoenixcontact.com/us/products/2970057>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com