

DC to 30GHz Broadband MMIC Low-Noise Amplifier

Description

The UATM30M2C is an eight stage traveling wave amplifier. The amplifier has been designed for low noise, flat gain, and good return loss to 30GHz. The amplifier typically has 2.5dB NF and 18dB gain from 6-20GHz, and 16dB gain from 0.04-30GHz.

Application

The UATM30M2C Broadband MMIC Low-Noise Amplifier is designed for low-noise and broadband flat-gain applications in RF and microwave communications, test equipment and military systems. By using specific external components, the bandwidth of operation can be extended below 40MHz.

Features

The UATM30M2C has >30dB dynamic gain control, and includes a temperature-referenced power detector output.

Device Highlights

- Low noise, ultra-flat gain 6-20GHz:
 - 2.5dB NF, 18 ± 0.3 dB gain
- Excellent 1.5-20GHz performance:
 - Very flat gain (18 ± 0.6 dB)
 - High Psat at 20GHz (20dBm)
 - High P1dB at 20GHz (17dBm)
- Wideband operation: 0.04-30GHz
- Good input / output return loss
- High isolation
- >30dB dynamic gain control
- Integrated power detector
- 100% DC, RF, and visually tested
- Size: 2390x920um (94.1x36.2mil)

Key Characteristics

Vdd=5.0V, Idd=150mA, Zo=50Ω

Specifications pertain to wafer measurements with RF probes and DC bias cards @ 25°C

		6 - 20GHz			1.5 - 20GHz			0.04 - 30GHz		
Parameter	Description	Min	Typ	Max	Min	Typ	Max	Min	Typ	Max
S21 (dB)	Small Signal Gain	16.5	18		16.5	18		14.5	16	
Flatness (±dB)	Gain Flatness		0.3	0.6		0.6	1.0		1.5	2.0
S11 (dB)	Input Match		-16	-13		-16	-13		-10	-8
S22 (dB)	Output Match		-18	-15		-18	-15		-18	-15
S12 (dB)	Reverse Isolation		-35	-30		-35	-30		-30	-25
P1dB (dBm)	1dB Compressed Output Power	16	17		16	17		12	13.5	
Psat (dBm)	Saturated Output Power	19	20		19	20		14	16.5	
Pout @16dB (dBm)	Output Power at 16dB Gain	17	18.5		17	18.5				
NF (dB)	Noise Figure		2.5			5			5.5	
RF _{det} (mV/mW)	RF Detector Sensitivity		0.5			0.5			0.5	

UATM30M2C Datasheet

UATM30M2C S21




Figure 1: Typical IC performance measured on-wafer

UATM30M2C Noise Figure




Figure 2: Typical IC performance with package de-embedded

UATM30M2C S11, S22




Figure 3: Typical IC performance measured on-wafer

UATM30M2C S12




Figure 4: Typical IC performance measured on-wafer

UATM30M2C Output Power




Figure 5: Typical IC performance measured on-wafer

UATM30M2C Group Delay




Figure 6: Typical IC performance measured on-wafer

Supplemental Specifications

Parameter	Description	Min	Typ	Max
Vdd	Drain Bias Voltage	3V	5V	8V
Idd	Drain Bias Current	—	150mA	250mA
Vg1	1 st Gate Bias Voltage	-4V	N/C	0V
Vg2	2 nd Gate Bias Voltage	Vdd-Vg2<7V	-	+4V
P _{in}	Input Power (CW)			20dBm
P _{dc}	Power Dissipation		0.755W	
T _{ch}	Channel Temperature			150°C
Θ _{ch}	Thermal Resistance (T _{case} =85°C)		18°C/W	

DC Bias

The UATM30M2C is biased by applying a positive voltage to the drain (Vdd), then setting the drain current (Idd) using a negative voltage on the gate (Vg1).

When zero volts is applied to the gate, the drain to source channel is open; this results in high Idd. When Vg1 is biased negatively, the channel is pinched off and Idd decreases.

The nominal bias is Vdd=5.0V, Idd=150mA. Improved noise or power performance can be achieved with application-specific biasing.

Gain Control

Dynamic gain control is available when operating the amplifier in the linear gain region. Negative voltage applied to the second gate (Vg2) reduces amplifier gain.

RF Power Detection

RF output power can be calculated from the difference between the RF detector voltage and the DC detector voltage, minus a DC offset. Please consult the power detector application note available from the Centellax webpage.

Low-Frequency Use

The UATM30M2C has been designed so that the bandwidth can be extended to low frequencies. The low end corner frequency of the device is primarily determined by the external biasing and AC coupling circuitry.

Matching

The amplifier incorporates on-chip termination resistors on the RF input and output. These resistors are RF grounded through on-chip capacitors, which are small and become open circuits at frequencies below 1GHz.

A pair of gate and drain termination bypass pads are provided for connecting external capacitors required for the low frequency extension network. These capacitors should be 10x the value of the DC blocking capacitors.

DC Blocks

The amplifier is DC coupled to the RF input and output pads; DC voltage on these pads must be isolated from external circuitry.

For operation above 2GHz, a series DC-blocking capacitor with minimum value of 20pF is recommended; operation above 40MHz requires a minimum of 120pF.

Biasing Inductor

DC bias applied to the drain (Vdd) must be decoupled with an off-chip RF choke inductor. The amount of bias inductance will determine the low frequency operating point. Inductive biasing can also be applied to the chip through the RF output.

For many applications above 2GHz, a bondwire from the Vdd pad will suffice as the biasing inductor. Ensure the correct bond length as shown in the assembly diagrams.

Simplified Circuit Schematic




Figure 7: Simplified Circuit Schematic

UATM30M2C Datasheet




Figure 8: Die size, pad locations, and pad descriptions

Pick-up and Chip Handling:

This MMIC has exposed air bridges on the top surface. **Do not pick up chip with vacuum on the die center;** handle from edges or with a custom collet.

Thermal Heat Sinking:

To avoid damage and for optimum performance, you must observe the maximum channel temperature and ensure adequate heat sinking.

ESD Handling and Bonding:

This MMIC is ESD sensitive; preventive measures should be taken during handling, die attach, and bonding.

Epoxy die attach is recommended. Please review our application note [AN01](#) GaAs MMIC handling and die attach recommendations, on our website for more handling, die attach and bonding information.

The information contained herein is believed to be accurate and is provided "AS IS, WHERE IS", with all faults and the entire risk associated with its use being entirely with the user. Centellax makes no representation with respect to the merchantability of the products or their suitability or fitness for any particular purpose or use. The information contained herein or any use of such information does not grant, explicitly or implicitly, to any party any patent rights, licenses, or any other intellectual property rights, whether with regard to such information itself or anything described by such information.