




PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
A	DCN 54066	03/24	SEE PDM



NOTES:
FOR A FOOTPRINT RECOMMENDATION SPECIFIC TO YOUR PCB,
PLEASE CONTACT US AT applications@svmicro.com

MATERIAL:

BODY & SHROUDS:	STAINLESS STEEL PER AMS-5640, ALLOY UNS S30300, TYPE 1
CONTACTS:	BERYLLIUM COPPER PER ASTM B196, ALLOY No. UNS C17300, TD04
INSULATORS:	PTFE PER ASTM D1710, TYPE I, GRADE 1, CLASS B
FINISH:	
BODY, SHROUDS, & CONTACTS:	GOLD PER ASTM B488, TYPE II, CODE C, CLASS 1.27, OVER NICKEL PER AMS-QQ-N-290, CLASS 1, .00005" MIN.

PERFORMANCE:

IMPEDANCE:	50 OHMS
FREQ. RANGE:	DC TO 65 GHz
VSWR:	1.25:1 DC TO 40 GHz 1.40:1 40 GHz TO 65 GHz
INSERTION LOSS:	.10 X SQRT(F(F IN GHz))
SHROUD TO BODY RETENTION:	8 LBS MIN (AXIAL)

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: $\pm 1/64$ ANGULAR: X° $\pm 1^{\circ}0'$
-----------	-----------	--