




PRODUCT NUMBER	PITCH
YK333xx0x0J0G	8.25 mm



MATERIALS & ELECTRICAL
 RATED VOLTAGE & CURRENT: 300 V, 20 A / 300 V, 32 A
 WITHSTAND VOLTAGE: AC 2500V/Min
 INSULATION RESISTANCE: 1000 MΩ OR MORE AT DC 500 V
 OPERATING TEMPERATURE RANG: -40 °C +115 °C
 SCREW TORQUE VALUE: 8.8 Lb-In
 WIRE RANGE: 22 - 12 AWG
 1) HOUSING: Thermoplastic, UL 94 V-0 BLACK
 2) TERMINAL: BRASS, 0.8t
 3) TERMINAL SCREWS: STEEL, M3
 APPROVAL:  

DIMENSION

Dim A	N×8.25±2.0
Dim B	(N-1)×8.25

N=Number of poles

Poles	Tolerance
2p-5p	±0.20
6p-10p	±0.25
11p-16p	±0.35
17p-24p	±0.40
25p-32p	±0.50

PART NO.: YK 333xx 0 x 0 J0G

No. of poles
 02 2 poles
 03 3 poles

 32 32 poles

Plated

Code	Terminal	Screw
0	G/F	G/F
1	G/F	Zinc
2	Tin	G/F
3	Tin	Zinc

RoHS compliant
 (lead<4%)
 In copper Alloy

mat'l. code				surface	tolerance	projection	product family		
ltr				ecn no	dr	date	TERMINAL BLOCK		
				tolerances unless otherwise specified			title		
				angles	X.±0.5		TERMINAL BLOCK		
				total	X.X±0.3		BARRIER TYPE		
				X'±1"	X.XX±0.1		scale		
				dr	EVAN LU	061614	MM		
				enr	EVAN LU	061614	FCI		
				chr	HANKE FENG	061614	dwg no		
				appd	SHI JUN	061614	YK333xx0x0J0G		
							type		
							CUSTOMER Drawing		
sheet index				revision sheet	A	1			