

UNIT:mm

REVISION INFORMATION			
Rev.	Rev. Date	Modified By	Brief Description
A/0	18-08-29	T0829B	NEW DRAWING
A/1	19-12-11	B1201A	increase DRAWING



PIN ASSIGNMENT:




CABLE WHITE PRINT

E166160 AWM 2725 80℃ 30V

28AWGX1P+24AWGX2C USB2.0


Electrical test:
1.100% short,open,miswire test
2.Conduct resistance:5 Ohm(max)
3.Insulation resistance:5Mohm(min)
4.dielectric test:DC 300V

PART NO	WIRE LENGTH "L"	BUYER COLOR	VENDOR COLOR	CUT LENGTH
102-1020-BE-00300	3000±50		IV-29#	3000-3010MM
102-1020-BE-00100	1000±30		IV-29#	1000-1010MM
102-1020-BE-00200	2000±30		IV-29#	2000-2010MM
102-1020-BE-00500	5000±60		IV-29#	5000-5010MM



1PCS/PE BAG

102-1020-BE-00500



1PCS/PE BAG

102-1020-BE-00100

102-1020-BE-00200

102-1020-BE-00300

NO.	NAME	Q'TY	SPECIFICATION
⑥	PE BAG	1/5	102-1020-BE-00500 CLEAR SIZE:280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"5PCS"
		1/10	102-1020-BE-00100 102-1020-BE-00200 102-1020-BE-00300 CLEAR SIZE:280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS"
⑤	PE BAG	1	CLEAR SIZE:130*230*0.05mm PRINT BLACK"MADE IN CHINA"+1PC"
④	TIE	1	WHITE A/B:L=100mm, C/D:L=120mm
③	OUT JACKET	12g	BEIGE(IV-29#)PVC-55P (MOULD NO:2002-527)
②	CABLE	1	BEIGE(IV-29#)USB2.0 UL2725 28#/1P+24#/2C+AEB OD:4.7mm
①	CONN	2	USB2.0 A MALE NICKEL PIN G/F 3PCS TYPE INSULATOR COLOR:WHITE

CnC Tech, LLC

Industrial Cable and Connector Technology

DRAWN BY:	DATE: 2019/12/11	DESCRIPTION: 4C CABLE USB A/M+A/M	
CHECKED BY:	SHEET 1 of 1	ITEM NO. As above	
APPROVED BY:	SCALE 1:1	REV. A/1	UNIT: mm

Downloaded from Arrow.com.