



**Part Number :** [734040814](#)  
**Product Description :** FAKRA Jack, Right-Angle, PCB Receptacle, Through Hole, Die Cast and Brass Body, Tin (Sn) Plated, Anti-tip Feature, Keying Code E/Green, 50 Ohms  
**Series Number :** 73403  
**Status :** Active  
**Product Category :** RF / Coaxial Connectors



## Documents & Resources

### Drawings

[734040814 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2020)9139-DC (19 Jan 2021)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### [Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

### [Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	RF / Coaxial Connectors
Series	73403
Description	FAKRA Jack, Right-Angle, PCB Receptacle, Through Hole, Die Cast and Brass Body, Tin (Sn) Plated, Anti-tip Feature, Keying Code E/ Green, 50 Ohms
Application	Automotive, RF
Product Name	FAKRA,SMB
Style	PCB
Type	Subminiature
UPC	756054162453

### Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 335 Vrms@Sea Level

### Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	Yes
Net Weight	6.328/g
Orientation	Right Angle

Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Through Hole
PCB Thickness - Recommended	2.40mm
Reverse Polar	No
Wire/Cable Type	N/A

**Solder Process Data**

Lead-Free Process Capability	SMC&WAVE
Max-Temp	260

---

This document was generated on Sep 23, 2025