

REVISIONS																			
LTR	DESCRIPTION										DATE (YR-MO-DA)				APPROVED				
A	Changes in accordance with NOR 5962-R068-92										91-12-05				Monica L. Poelking				
B	Changes in accordance with NOR 5962-R170-92										92-04-17				Monica L. Poelking				
C	Changes in accordance with NOR 5962-R131-93										93-04-12				Monica L. Poelking				
D	Revise for "QD" certification. New boilerplate. Editorial changes throughout. - ljs										00-02-17				Raymond Monnin				
E	Correct page 2 generic. Editorial changes on pages 1 and 4. -les										02-05-01				Raymond Monnin				
The original first page of this drawing has been replaced.																			
REV																			
SHEET																			
REV																			
SHEET																			
REV STATUS					REV		E	E	E	E	E	E	E	E	E	E	E	E	
OF SHEETS					SHEET		1	2	3	4	5	6	7	8	9	10	11	12	
PMIC N/A					PREPARED BY Monica L. Grosel					DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43216									
STANDARD MICROCIRCUIT DRAWING THIS DRAWING IS AVAILABLE FOR USE BY ALL DEPARTMENTS AND AGENCIES OF THE DEPARTMENT OF DEFENSE AMSC N/A					CHECKED BY D. A. DiCenzo														
					APPROVED BY N. A. Hauck					MICROCIRCUIT, DIGITAL, ECL, QUAD 2-INPUT NONINVERTING MULTIPLEXER, MONOLITHIC SILICON									
					DRAWING APPROVAL DATE 24 July 1987														
					REVISION LEVEL E					SIZE A	CAGE CODE 67268			5962-87566					
										SHEET 1 OF 12									

1. SCOPE

1.1 Scope. This drawing describes device requirements for MIL-STD-883 compliant, non-JAN class level B microcircuits in accordance with MIL-PRF-38535, appendix A.

1.2 Part or Identifying Number (PIN). The complete PIN is as shown in the following example:

<u>5962-87566</u>	<u>01</u>	<u>E</u>	<u>X</u>
Drawing number	Device type (see 1.2.1)	Case outline (see 1.2.2)	Lead finish (see 1.2.3)

1.2.1 Device type(s). The device type(s) identify the circuit function as follows:

<u>Device type</u>	<u>Generic number</u>	<u>Circuit function</u>
01	10H558	Quad, two-input, noninverting multiplexer

1.2.2 Case outline(s). The case outline(s) are as designated in MIL-STD-1835 and as follows:

<u>Outline letter</u>	<u>Descriptive designator</u>	<u>Terminals</u>	<u>Package style</u>
E	GDIP1T-16 or CDIP2-T16	16	dual-in-line
F	GDFP2-F16 or GDFP3-F16	16	flat package
2	CQCC1-N20	20	square chip carrier

1.2.3 Lead finish. The lead finish is as specified in MIL-PRF-38535, appendix A.

1.3 Absolute maximum ratings.

Supply voltage range	-8.0 V dc to 0.0 V dc
Input voltage range	0.0 V to -5.2 V dc
Storage temperature range	-65°C to +165°C
Lead temperature (soldering, 10 seconds)	+300°C
Junction temperature (T_J)	+165°C
Maximum power dissipation (P_D)	320 mW
Thermal resistance, junction-to-case (θ_{JC})	See MIL-STD-1835

1.4 Recommended operating conditions.

Supply voltage range (V_{CC})	-5.46 V minimum to -4.94 V maximum
Ambient operating temperature range (T_A)	-55°C to +125°C
Minimum high level input voltage (V_{IH}):	
$T_A = +25^\circ\text{C}$	-0.780 V dc
$T_A = +125^\circ\text{C}$	-0.650 V dc
$T_A = -55^\circ\text{C}$	-0.840 V dc
Maximum low level input voltage (V_{IL})	-1.950 V dc

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43216-5000	SIZE A		5962-87566
		REVISION LEVEL E	SHEET 2

2. APPLICABLE DOCUMENTS

2.1 Government specification, standards, and handbooks. The following specification, standards, and handbooks form a part of this drawing to the extent specified herein. Unless otherwise specified, the issues of these documents are those listed in the issue of the Department of Defense Index of Specifications and Standards (DoDISS) and supplement thereto, cited in the solicitation.

SPECIFICATION

DEPARTMENT OF DEFENSE

MIL-PRF-38535 - Integrated Circuits, Manufacturing, General Specification for.

STANDARDS

DEPARTMENT OF DEFENSE

MIL-STD-883 - Test Method Standard Microcircuits.
MIL-STD-1835 - Interface Standard For Microcircuit Case Outlines.

HANDBOOKS

DEPARTMENT OF DEFENSE

MIL-HDBK-103 - List of Standard Microcircuit Drawings (SMD's).
MIL-HDBK-780 - Standard Microcircuit Drawings.

(Unless otherwise indicated, copies of the specification, standards, and handbooks are available from the Standardization Document Order Desk, 700 Robbins Avenue, Building 4D, Philadelphia, PA 19111-5094.)

2.2 Order of precedence. In the event of a conflict between the text of this drawing and the references cited herein, the text of this drawing takes precedence. Nothing in this document, however, supersedes applicable laws and regulations unless a specific exemption has been obtained.

3. REQUIREMENTS

3.1 Item requirements. The individual item requirements shall be in accordance with MIL-PRF-38535, appendix A for non-JAN class level B devices and as specified herein. Product built to this drawing that is produced by a Qualified Manufacturer Listing (QML) certified and qualified manufacturer or a manufacturer who has been granted transitional certification to MIL-PRF-38535 may be processed as QML product in accordance with the manufacturers approved program plan and qualifying activity approval in accordance with MIL-PRF-38535. This QML flow as documented in the Quality Management (QM) plan may make modifications to the requirements herein. These modifications shall not affect form, fit, or function of the device. These modifications shall not affect the PIN as described herein. A "Q" or "QML" certification mark in accordance with MIL-PRF-38535 is required to identify when the QML flow option is used. This drawing has been modified to allow the manufacturer to use the alternate die/fabrication requirements of paragraph A.3.2.2 of MIL-PRF-38535 or other alternative approved by the Qualifying Activity.

3.2 Design, construction, and physical dimensions. The design, construction, and physical dimensions shall be as specified in MIL-PRF-38535, appendix A and herein.

3.2.1 Case outlines. The case outlines shall be in accordance with 1.2.2 herein.

3.2.2 Terminal connections. The terminal connections shall be as specified on figure 1.

3.2.3 Truth table. The truth table shall be as specified on figure 2.

3.2.4 Logic diagram. The logic diagram shall be as specified on figure 3.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43216-5000	SIZE A		5962-87566
		REVISION LEVEL E	SHEET 3

3.2.4 Test circuit and switching waveforms. The test circuit and switching waveforms shall be as specified on figure 4.

3.3 Electrical performance characteristics. Unless otherwise specified herein, the electrical performance characteristics are as specified in table I and shall apply over the full ambient operating temperature range.

3.4 Electrical test requirements. The electrical test requirements shall be the subgroups specified in table II. The electrical tests for each subgroup are described in table I.

3.5 Marking. Marking shall be in accordance with MIL-PRF-38535, appendix A. The part shall be marked with the PIN listed in 1.2 herein. In addition, the manufacturer's PIN may also be marked as listed in MIL-HDBK-103 (see 6.6 herein). For packages where marking of the entire SMD PIN number is not feasible due to space limitations, the manufacturer has the option of not marking the "5962-" on the device.

3.5.1 Certification/compliance mark. The certification mark for device classes Q and V shall be a "QML" or "Q" as required in MIL-PRF-38535. The compliance mark for device class M shall be a "C" as required in MIL-PRF-38535, appendix A. For class Q product built in accordance with A.3.2.2 of MIL-PRF-38535, or as modified in the manufacturer's Quality Management (QM) Plan, the "QD" certification mark shall be used in place of the "QML" or "Q" certification mark.

3.6 Certificate of compliance. A certificate of compliance shall be required from a manufacturer in order to be listed as an approved source of supply in MIL-HDBK-103 (see 6.6 herein). The certificate of compliance submitted to DSCC-VA prior to listing as an approved source of supply shall affirm that the manufacturer's product meets the requirements of MIL-PRF-38535, appendix A and the requirements herein.

3.7 Certificate of conformance. A certificate of conformance as required in MIL-PRF-38535, appendix A shall be provided with each lot of microcircuits delivered to this drawing.

3.8 Notification of change. Notification of change to DSCC-VA shall be required in accordance with MIL-PRF-38535, appendix A.

3.9 Verification and review. DSCC, DSCC's agent, and the acquiring activity retain the option to review the manufacturer's facility and applicable required documentation. Offshore documentation shall be made available onshore at the option of the reviewer.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43216-5000	SIZE A		5962-87566
		REVISION LEVEL E	SHEET 4

TABLE I. Electrical performance characteristics.

Test	Symbol	Conditions -55°C ≤ T _A ≤+125°C unless otherwise specified	Group A subgroups	Limits		Unit		
				Min	Max			
Cases E, F and 2								
Quiescent conditions 1/								
High level output voltage	V _{OH}	Outputs terminated through 100Ω to −2 V	V _{IH}	V _{IL}	1 2 3	-1.010 -0.860 -1.060	-0.780 -0.650 -0.840	V
			-0.780	-1.950				
			-0.650	-1.950				
Low level output voltage	V _{OL}	V _{CC} = 0.0 V V _{EE} = -5.2 V	-0.840	-1.950	1 2 3	-1.950 -1.950 -1.950	-1.580 -1.565 -1.610	V
			-0.780	-1.950				
			-0.650	-1.950				
High level threshold output voltage	V _{OHA}	3/	-1.110	-1.480	1 2 3	-1.010 -0.860 -1.060	-0.780 -0.650 -0.840	V
			-0.960	-1.465				
			-1.160	-1.510				
Low level threshold output voltage	V _{OLA}		-1.110	-1.480	1 2 3	-1.950 -1.950 -1.950	-1.580 -1.565 -1.610	V
			-0.960	-1.465				
			-1.160	-1.510				
Power supply drain current	I _{EE} 4/	Outputs terminated through 100Ω to −2 V V _{CC} = 0.0 V V _{EE} = -5.2 V			1	-48		mA
					2, 3	-53		
High level input current	I _{IH1}	Outputs terminated through 100Ω to −2 V	Select		1, 2 3		295 475	μA
	I _{IH2}		All inputs		1, 2 3		320 515	μA
Low level input current	I _{IL}	All inputs			1, 3 2	0.5 0.3		μA
Cases E and F								
DC rapid conditions 2/								
High level output voltage	V _{OH}	Outputs terminated through 100Ω to −2.0 V V _{CC} = 0.0 V	V _{IH}	V _{IL}	1 2 3	-1.022 -0.874 -1,074	-0.793 -0.665 -0.855	V
			-0.793	-1.950				
			-0.665	-1.950				
Low level output voltage	V _{OL}	V _{EE} = -5.2 V 3/	-0.855	-1.950	1 2 3	-1.950 -1.950 -1.950	-1.584 -1.570 -1.615	V
			-0.793	-1.950				
			-0.665	-1.950				

See footnotes at end of table.

**STANDARD
MICROCIRCUIT DRAWING**
DEFENSE SUPPLY CENTER COLUMBUS
COLUMBUS, OHIO 43216-5000

SIZE
A

REVISION LEVEL
E

5962-87566
SHEET
5

TABLE I. Electrical performance characteristics. - continued

Test	Symbol	Conditions -55°C ≤ T _A ≤ +125°C unless otherwise specified	Group A subgroups	Limits		Unit		
				Min	Max			
Cases E and F								
DC rapid conditions 2/								
			V _{IH}	V _{IL}				
High level threshold output voltage	V _{OHA}	Outputs terminated through 100Ω to −2 V V _{CC} = 0.0 V	-1.122	-1.484	1	-1.022	-0.793	V
			-0.974	-1.470	2	-0.874	-0.665	
			-1.174	-1.515	3	-1.074	-0.855	
Low level threshold output voltage	V _{OLA}	V _{EE} = -5.2 V 3/	-1.122	-1.484	1	-1.950	-1.584	V
			-0.974	-1.470	2	-1.950	-1.570	
			-1.174	-1.515	3	-1.950	-1.615	
Power supply drain current	I _{EE} 4/	Outputs terminated through 100Ω to −2 V V _{CC} = 0.0 V V _{EE} = -5.2 V			1 2, 3	-47 -52		mA
High level input current	I _{IH1}	Outputs terminated through 100Ω to −2 V V _{EE} = -5.2 V V _{CC} = 0.0 V	Select		1, 2 3		280 460	μA
	All inputs		1, 2 3		305 500	μA		
Low level input current	I _{IL}	All inputs			1, 3 2	0.5 0.3		μA

Case 2

DC rapid conditions 2/

High level output voltage	V _{OH}	Outputs terminated through 100Ω to -2 V V _{CC} = 0.0 V V _{EE} = -5.2 V	V _{IH}	V _{IL}				
			-0.800	-1.950	1	-1.028	-0.800	V
			-0.671	-1.950	2	-0.880	-0.671	
Low level output voltage	V _{OL}	3/	-0.861	-1.950	3	-1.080	-0.861	
			-0.800	-1.950	1	-1.950	-1.586	V
			-0.671	-1.950	2	-1.950	-1.572	
High level threshold output voltage	V _{OHA}	3/	-0.861	-1.950	3	-1.950	-1.617	
			-1.128	-1.486	1	-1.028	-0.800	V
			-0.980	-1.472	2	-0.880	-0.671	
Low level threshold output voltage	V _{OLA}	3/	-1.180	-1.517	3	-1.080	-0.861	
			-1.128	-1.486	1	-1.950	-1.586	V
			-0.980	-1.472	2	-1.950	-1.572	
Power supply drain current	I _{EE} 4/	Outputs terminated through 100Ω to -2 V V _{CC} = 0.0 V V _{EE} = -5.2 V	-1.180	-1.517	3	-1.950	-1.617	
					1	-47		mA
					2, 3	-52		

See footnotes at end of table.

STANDARD
MICROCIRCUIT DRAWING
 DEFENSE SUPPLY CENTER COLUMBUS
 COLUMBUS, OHIO 43216-5000

SIZE
A

REVISION LEVEL
 E

5962-87566

SHEET
6

TABLE I. Electrical performance characteristics. - continued

Test	Symbol	Conditions -55°C ≤ T _A ≤ +125°C unless otherwise specified		Group A subgroups	Limits		Unit
					Min	Max	
High level input current	I _{IH1}	Outputs terminated through 100Ω to -2 V V _{EE} = -5.2 V V _{CC} = 0.0 V	Select	1, 2 3		280 460	μA
	I _{IH2}		All inputs	1, 2 3		305 500	μA
Low level input current	I _{IL}	All inputs		1, 3 2	0.5 0.3		μA

Cases E, F, and 2

AC test conditions

Transition time	t _{TLH}	V _{EE} = -2.94 V V _{CC} = 2.0 V C _L ≤ 5 pF	9	0.70	2.00	ns
	t _{THL}		10	0.70	2.20	
	t ₊ , t ₋		11	0.70	2.20	
Propagation delay time	t _{PHH1} , t _{PLL1} , t _{PHL1} , t _{PLH1}	Load all outputs through 100 Ω to GND See figure 4	9	0.50	1.80	ns
			10	0.50	2.20	
			11	0.50	1.90	
Propagation delay time	t _{PHH2} , t _{PLL2} , t _{PHL2} , t _{PLH2}		9	1.00	2.70	ns
			10	1.00	3.00	
			11	1.00	2.70	

1/ The quiescent limits are determined after a device has reached thermal equilibrium. This is defined as the reading taken with the device in a socket with ≥ 500 LFPM of +25°C air blowing on the unit and with power applied at least four minutes before the reading is taken.

2/ The dc rapid test forcing functions and limits are used for all dc testing. These limits are determined for each device type based on the power dissipation and package type. The rapid test (delta V) limits and forcing functions are skewed allowing rapid testing to be performed at standard temperatures without the addition of delta T's.

3/ The high and low level output current varies with temperature, and shall be calculated using the following formulas:

$$I_{OH} = (-2.0 \text{ V} - V_{OH})/100\Omega, \quad I_{OL} = (-2.0 \text{ V} - V_{OL})/100\Omega$$

4/ The I_{EE} limits, although specified in the minimum column, shall not be exceeded, in magnitude, as a maximum value.

**STANDARD
MICROCIRCUIT DRAWING**
DEFENSE SUPPLY CENTER COLUMBUS
COLUMBUS, OHIO 43216-5000

SIZE
A

5962-87566

REVISION LEVEL
E

SHEET

7

Case outlines	E	F	2
Terminal number	Terminal symbol		
1	Y_1	C_1	NC
2	Y_2	Y_4	Y_1
3	B_0	Y_3	Y_2
4	B_1	V_{CC}	B_0
5	A_0	Y_1	B_1
6	A_1	Y_2	NC
7	NC	B_0	A_0
8	V_{EE}	B_1	A_1
9	SELECT	A_0	NC
10	D_0	A_1	V_{EE}
11	D_1	NC	NC
12	C_0	V_{EE}	SELECT
13	C_1	SELECT	D_0
14	Y_4	D_0	D_1
15	Y_3	D_1	C_0
16	V_{CC}	C_0	NC
17	---	---	C_1
18	---	---	Y_4
19	---	---	Y_3
20	---	---	V_{CC}

NC = No connection

FIGURE 1. Terminal connections.

Select	X_0	X_1	Output
L	ϕ	L	L
L	ϕ	H	H
H	L	ϕ	L
H	H	ϕ	H

ϕ = Don't care
X = A, B, C or D

FIGURE 2. Truth table.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43216-5000	SIZE A		5962-87566
		REVISION LEVEL E	SHEET 8





FIGURE 3. Logic diagram.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43216-5000	SIZE A		5962-87566
		REVISION LEVEL E	SHEET 9



NOTES:

1. Pulse generator characteristics:
PRR = 1 MHz, $t_{THL} = t_{TLH} = 1.0 \pm 0.2$ ns (20% to 80%), duty cycle = 50 percent.
2. The 50 Ω resistor in series with the 50 Ω coaxial constitutes the 100 Ω load.

FIGURE 4. Test circuit and switching waveforms.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43216-5000	SIZE A		5962-87566
		REVISION LEVEL E	SHEET 10

4. QUALITY ASSURANCE PROVISIONS

4.1 Sampling and inspection. Sampling and inspection procedures shall be in accordance with MIL-PRF-38535, appendix A.

4.2 Screening. Screening shall be in accordance with method 5004 of MIL-STD-883, and shall be conducted on all devices prior to quality conformance inspection. The following additional criteria shall apply:

- a. Burn-in test, method 1015 of MIL-STD-883.
 - (1) Test condition A, B, C or D. The test circuit shall be maintained by the manufacturer under document revision level control and shall be made available to the preparing or acquiring activity upon request. The test circuit shall specify the inputs, outputs, biases, and power dissipation, as applicable, in accordance with the intent specified in test method 1015 of MIL-STD-883.
 - (2) $T_A = +125^{\circ}\text{C}$, minimum.
- b. Interim and final electrical test parameters shall be as specified in table II herein, except interim electrical parameter tests prior to burn-in are optional at the discretion of the manufacturer.

TABLE II. Electrical test requirements.

MIL-STD-883 test requirements	Subgroups (in accordance with MIL-STD-883, method 5005, table I)
Interim electrical parameters (method 5004)	1
Final electrical test parameters (method 5004)	1*, 2, 3, 7*, 9
Group A test requirements (method 5005)	1, 2, 3, 7, 9, 10, 11
Groups C and D end-point electrical parameters (method 5005)	1, 2, 3

* PDA applies to subgroups 1 and 7.

4.3 Quality conformance inspection. Quality conformance inspection shall be in accordance with method 5005 of MIL-STD-883 including groups A, B, C, and D inspections. The following additional criteria shall apply.

4.3.1 Group A inspection.

- a. Tests shall be as specified in table II herein.
- b. Subgroups 4, 5, 6 and 8 in table I, method 5005 of MIL-STD-883 shall be omitted.
- c. Subgroup 7 shall include verification of the truth table.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43216-5000	SIZE A		5962-87566
		REVISION LEVEL E	SHEET 11

4.3.2 Groups C and D inspections.

- a. End-point electrical parameters shall be as specified in table II herein.
- b. Steady-state life test conditions, method 1005 of MIL-STD-883.
 - (1) Test condition A, B, C or D. The test circuit shall be maintained by the manufacturer under document revision level control and shall be made available to the preparing or acquiring activity upon request. The test circuit shall specify the inputs, outputs, biases, and power dissipation, as applicable, in accordance with the intent specified in test method 1005 of MIL-STD-883.
 - (2) $T_A = +125^{\circ}\text{C}$, minimum.
 - (3) Test duration: 1,000 hours, except as permitted by method 1005 of MIL-STD-883.

5. PACKAGING

5.1 Packaging requirements. The requirements for packaging shall be in accordance with MIL-PRF-38535, appendix A.

6. NOTES

6.1 Intended use. Microcircuits conforming to this drawing are intended for use for Government microcircuit applications (original equipment), design applications, and logistics purposes.

6.2 Replaceability. Microcircuits covered by this drawing will replace the same generic device covered by a contractor-prepared specification or drawing.

6.3 Configuration control of SMD's. All proposed changes to existing SMD's will be coordinated with the users of record for the individual documents. This coordination will be accomplished using DD Form 1692, Engineering Change Proposal.

6.4 Record of users. Military and industrial users shall inform Defense Supply Center Columbus when a system application requires configuration control and the applicable SMD. DSCC will maintain a record of users and this list will be used for coordination and distribution of changes to the drawings. Users of drawings covering microelectronics devices (FSC 5962) should contact DSCC-VA, telephone (614) 692-0544.

6.5 Comments. Comments on this drawing should be directed to DSCC-VA, Columbus, Ohio 43216-5000, or telephone (614) 692-0547.

6.6 Approved sources of supply. Approved sources of supply are listed in MIL-HDBK-103. The vendors listed in MIL-HDBK-103 have agreed to this drawing and a certificate of compliance (see 3.6 herein) has been submitted to and accepted by DSCC-VA.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43216-5000	SIZE A		5962-87566
		REVISION LEVEL E	SHEET 12

STANDARD MICROCIRCUIT DRAWING BULLETIN

DATE: 02-05-01

Approved sources of supply for SMD 5962-87566 are listed below for immediate acquisition information only and shall be added to MIL-HDBK-103 and QML 38535 during the next revision. MIL-HDBK-103 and QML 38535 will be revised to include the addition or deletion of sources. The vendors listed below have agreed to this drawing and a certificate of compliance has been submitted to and accepted by DSCC-VA. This bulletin is superseded by the next dated revision of MIL-HDBK-103 and QML 38535.

Standard microcircuit drawing PIN <u>1</u> /	Vendor CAGE number	Vendor similar PIN <u>2</u> /
5962-8756601EA	0C7V7 <u>3</u> /	10H558/EA 10558/BEAJC
5962-8756601FA	0C7V7 <u>3</u> /	10H558/FA 10558/BFAJC
5962-87566012A	0C7V7 <u>3</u> /	10H558/2A 10558M/B2CJC

- 1/ The lead finish shown for each PIN representing a hermetic package is the most readily available from the manufacturer listed for that part. If the desired lead finish is not listed contact the vendor to determine its availability.
- 2/ Caution. Do not use this number for item acquisition. Items acquired to this number may not satisfy the performance requirements of this drawing.
- 3/ Not available from an approved source.

Vendor CAGE
number

0C7V7

Vendor name
and address

QP Labs
3605 Kifer Road
Santa Clara, CA 95051

The information contained herein is disseminated for convenience only and the Government assumes no liability whatsoever for any inaccuracies in the information bulletin.