

Data sheet

PT094xxHBBF Typ 392

Page 1/6

P/N

313921xx

xx=number of poles


2022/04/05

Version: A


Illustrations



Dimensional drawing



Drill pattern



See enlarged drawings at the end of document

Product specification

- pin header, solderable
- centerline 3.81 mm, direction of connection 90°
- closed ends
- color black, mounting flange
- codeable

U | Contact

Data sheet PT094xxHBBF Typ 392

Page 2/6

P/N
313921xx

xx=number of poles

2022/04/05

Version: A

Technical Data

General Data			
Solder pin length	3.5 mm		
min. number of poles	2		
max. number of poles	24		
Insulating material class	CTI 600		
clearance/creepage dist.	3.01 mm		
Protection category	IP00		
Rated current	9 A		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	200 V	500 V	500 V
Rated test voltage	4 kV	4 kV	4 kV
Approvals			
 V / A	300 / 8		
approval UL - File No.	E121004		
 1.5 mm²	160 V / 2.5 kV / 9 A / 0.8 x 0.8 mm		
Material			
insulating material	PA66		
flammability class	V0		
contact pin material	CuFe		
contact pin surface	Ni + Sn		
Thread insert	CuZnPb		
Glow-Wire Flammability GWFI	960 °C acc. to IEC 60695-2-12		
Glow-Wire Flammability GWIT	775 °C acc. to IEC 60695-2-13		
REACH	compliant		
REACH - substance (SVHC)	Lead / 7439-92-1		
Climatic Data			
upper limit temperature	105 °C		
lower limit temperature	-40 °C		
general			
Tolerance	ISO 2768 -mH		
Solderability	Acc. to JEDEC JESD22-B102E 245°C/5s		

U | Contact

Data sheet

PT094xxHBBF Typ 392

Page 3/6

P/N

313921xx

xx=number of poles

2022/04/05

Version: A

Accessories

P/N	Designation
720293-01-2	Coding Star for pin header, centerline 3.81 mm



U | Contact

Data sheet

Page 4/6

PT094xxHBBF Typ 392

P/N

313921xx**xx=number of poles**

2022/04/05

Version: A

Counterpart of

P/N	Designation
313791	RP034xxVBLF Typ 379
ASP084	SP064xxVGNF ASP084



U | Contact

Data sheet

PT094xxHBBF Typ 392

Page 5/6

P/N

313921xx


xx=number of poles

2022/04/05

Version: A

Illustrations

Dimensional drawing



$L = (\text{pole size} - 1) \times \text{centerline} + 13.95 \text{ mm} [0.549]$

U | Contact

Data sheet

PT094xxHBBF Typ 392

Page 6/6

P/N

313921xx

xx=number of poles

2022/04/05

Version: A

Illustrations

Drill pattern

