

Part Number : [760559607](#)

Product Description : Impact 100 Ohm 5 Pair Vertical Backplane Header, Right Guided, Left Endwall, 16 Columns, 240 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free

Series Number : 76055

Status : Active

Product Category : Backplane Connectors

Documents and Resources

Drawings

[760559607_sd.pdf](#)

[PK-70873-759-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[SYM-76055-9607-001.zip](#)

Specifications


[AS-76060-990-001.pdf](#)

[AS-76060-9999-001.pdf](#)

[PS-76060-999-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)

EU RoHS	Compliant per EU 2015/863
---------	---------------------------

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Backplane Connectors
Series	76055
Description	Impact 100 Ohm 5 Pair Vertical Backplane Header, Right Guided, Left Endwall, 16 Columns, 240 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free
Application	Conventional, Mezzanine
Component Type	PCB Header
Product Name	Impact
UPC	883906414924

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	0.75A
-------------------------------	-------

Data Rate	25.0 Gbps
Impedance	100Ω
Shielded	No
Shield Type	N/A
Voltage - Maximum	30V AC (RMS)/DC

Physical

Circuits (Loaded)	240
Circuits (maximum)	240
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	Yes
Keying to Mating Part	No
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	8.633/g
Number of Columns	16
Number of Pairs	5
Number of Rows	15
Orientation	Vertical
Packaging Type	Tray
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.00mm
PC Tail Length	1.40mm
Pitch - Mating Interface	1.90mm
Pitch - Termination Interface	1.90mm
Plating min - Mating	0.762μm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-55° to +85°C

Termination Interface Style	Through Hole - Compliant Pin
-----------------------------	------------------------------

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
Impact 100 Ohm 5 Pair Right-Angle Daughtercard Receptacles	<u>76060</u>

Application Tooling

This document was generated on May 20, 2026