

# HC-HS06-I-UT-F - Contact insert



1406530

<https://www.phoenixcontact.com/us/products/1406530>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, number of positions: 6+PE, size: B16, number of connections per position: 1, Socket, Screw connection, 400 V/690 V, 41 A, 0.5 mm<sup>2</sup> ... 6 mm<sup>2</sup>, application: Power

## Your advantages

- For fast coding with plastic profile<br/>
- Shock and vibration-resistant in accordance with DIN EN 61373

## Commercial data

Item number	1406530
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF61
Product key	AF7ABI
Catalog page	Page 563 (C-2-2019)
GTIN	4046356921350
Weight per piece (including packing)	91.5 g
Weight per piece (excluding packing)	91.5 g
Customs tariff number	85366990
Country of origin	CN

# HC-HS06-I-UT-F - Contact insert

1406530

<https://www.phoenixcontact.com/us/products/1406530>



## Technical data

### Notes

General	For HEAVYCON housing B16 and B32
General	Connectors may be operated only when there is no load/voltage.

### Mounting

Assembly note	To ensure correct use, installation in housing with IP54 protection or better is required
---------------	---


### Product properties

Product type	Contact insert with a fixed no. of positions
Series	HC-HS
Application	Power
Type	B16 B32
Number of positions	6
Connection profile	6+PE
Contact numbering	1 - 6
Number of connections per position	1
Contact material type	turned

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Dimensions

Dimensional drawing	
Width	34 mm
Height	34 mm
Length	84.5 mm
Drill hole distance, horizontal	77.5 mm
Drill hole distance, vertical	27 mm

### Mechanical characteristics

Contact diameter	3.5 mm
------------------	--------

### Connection data

#### Connection technology

Connection technology	Screw connection
Number of connections per position	1

# HC-HS06-I-UT-F - Contact insert



1406530

<https://www.phoenixcontact.com/us/products/1406530>

Connection in acc. with standard	IEC / EN
----------------------------------	----------

## Conductor connection

Conductor cross section	0.5 mm <sup>2</sup> ... 6 mm <sup>2</sup> (power contacts)
Connection cross section AWG	20 ... 10
Tightening torque	0.8 Nm ... 1.2 Nm (PE connection)
	0.5 Nm ... 0.8 Nm (Mounting screws for mounting in the HEAVYCON housing)
	1.2 Nm
Stripping length of the individual wire	10 mm

## Electrical properties

Rated voltage (III/3)	400 V (Conductor-PE)
	690 V (Conductor-Conductor)
Rated voltage for power contacts	400/690 V
Rated surge voltage	6 kV (power contacts)
Rated current	41 A (power contacts)
SCCR	5 kA (UL 2237)

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

## Material specifications

Flammability rating according to UL 94	V0
Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PC
Standards/regulations	PC

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C (including heating up of contacts)
---------------------------------	--

## Standards and regulations

### Testing

Standards/regulations	PC: Fire protection in rail vehicles - requirement sets R22, R23, and R24 acc. to DIN EN 45545-2 (Risk level HL1 - HL3)
-----------------------	---

# HC-HS06-I-UT-F - Contact insert




1406530

<https://www.phoenixcontact.com/us/products/1406530>


## Drawings

Dimensional drawing



Dimensional drawing

Dimensional drawing



Mounting cutout when used without housing


# HC-HS06-I-UT-F - Contact insert

1406530

<https://www.phoenixcontact.com/us/products/1406530>



Schematic diagram




Connector pin assignment, connection side

# HC-HS06-I-UT-F - Contact insert

1406530

<https://www.phoenixcontact.com/us/products/1406530>



Derating diagram

# HC-HS06-I-UT-F - Contact insert



1406530

<https://www.phoenixcontact.com/us/products/1406530>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1406530>

### DNV

Approval ID: TAE000037S



### CSA

Approval ID: 013631\_0\_000

	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	600 V	32 A	- 10	-



### UL Recognized

Approval ID: E118976

	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	600 V	35 A	-	-



### UL Recognized

Approval ID: E468743

	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	600 V	35 A	-	-

# HC-HS06-I-UT-F - Contact insert

1406530

<https://www.phoenixcontact.com/us/products/1406530>



## Classifications

### ECLASS

ECLASS-13.0	27440205
-------------	----------

### ETIM

ETIM 9.0	EC000438
----------	----------

### UNSPSC

UNSPSC 21.0	39121500
-------------	----------



# HC-HS06-I-UT-F - Contact insert



1406530  
<https://www.phoenixcontact.com/us/products/1406530>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)