
Cool MOS™ Power Transistor

V_{DS} @ T_{jmax}	560	V
$R_{DS(on)}$	0.38	Ω
I_D	11.6	A


Feature

- New revolutionary high voltage technology
- Ultra low gate charge
- Periodic avalanche rated
- Extreme d*v*/d*t* rated
- Ultra low effective capacitances
- Improved transconductance

PG-TO220FP PG-TO262 G-TO220



- PG-TO-220-3-31;-3-111: Fully isolated package (2500 VAC; 1 minute)
- Pb-free lead plating; RoHS compliant
- Qualified according to JEDEC[0)] for target applications



Type	Package	Ordering Code	Marking
SPP12N50C3	PG-TO220	Q67040-S4579	12N50C3
SPI12N50C3	PG-TO262	Q67040-S4578	12N50C3
SPA12N50C3	PG-TO220FP	SP000216322	12N50C3

Maximum Ratings

Parameter	Symbol	Value		Unit
		SPP_I	SPA	
Continuous drain current	I_D			A
T_C = 25 °C		11.6	11.6[1)]	
T_C = 100 °C		7	7[1)]	
Pulsed drain current, t_p limited by T_{jmax}	$I_{D\ puls}$	34.8	34.8	A
Avalanche energy, single pulse	E_{AS}	340	340	mJ
I_D=5.5A, V_{DD}=50V				
Avalanche energy, repetitive t_{AR} limited by T_{jmax}[2)]	E_{AR}	0.6	0.6	
I_D=11.6A, V_{DD}=50V				
Avalanche current, repetitive t_{AR} limited by T_{jmax}	I_{AR}	11.6	11.6	A
Gate source voltage	V_{GS}	±20	±20	V
Gate source voltage AC (f >1Hz)	V_{GS}	±30	±30	
Power dissipation, T_C = 25°C	P_{tot}	125	33	W
Operating and storage temperature	T_j , T_{stg}	-55...+150		°C
Reverse diode dv/dt [7)]	*dv/dt*	15		V/ns

Downloaded from Arrow.com.

Maximum Ratings

Parameter	Symbol	Value	Unit
Drain Source voltage slope V_{DS} = 400 V, I_D = 11.6 A, T_j = 125 °C	d*v*/d*t*	50	V/ns

Thermal Characteristics

Parameter	Symbol	Values			Unit
		min.	typ.	max.	
Thermal resistance, junction - case	R_{thJC}	-	-	1	K/W
Thermal resistance, junction - case, FullPAK	R_{thJC_FP}	-	-	3.8	
Thermal resistance, junction - ambient, leaded	R_{thJA}	-	-	62	
Thermal resistance, junction - ambient, FullPAK	R_{thJA_FP}	-	-	80	
SMD version, device on PCB: @ min. footprint @ 6 cm^2 cooling area [3]	R_{thJA}	 - -	 - 35	 62 -	
Soldering temperature, wavesoldering 1.6 mm (0.063 in.) from case for 10s [4]	T_{sold}	-	-	260	°C

Electrical Characteristics, at T_j=25°C unless otherwise specified

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Drain-source breakdown voltage	$V_{(BR)DSS}$	V_{GS}=0V, I_D=0.25mA	500	-	-	V
Drain-Source avalanche breakdown voltage	$V_{(BR)DS}$	V_{GS}=0V, I_D=11.6A	-	600	-	
Gate threshold voltage	$V_{GS(th)}$	I_D=500µA, V_{GS}=V_{DS}	2.1	3	3.9	
Zero gate voltage drain current	I_{DSS}	V_{DS}=500V, V_{GS}=0V, T_j=25°C T_j=150°C	 - -	 0.1 -	 1 100	µA
Gate-source leakage current	I_{GSS}	V_{GS}=20V, V_{DS}=0V	-	-	100	nA
Drain-source on-state resistance	$R_{DS(on)}$	V_{GS}=10V, I_D=7A T_j=25°C T_j=150°C	 - -	 0.34 0.92	 0.38 -	Ω
Gate input resistance	R_G	*f*=1MHz, open drain	-	1.4	-	

Downloaded from Arrow.com.

Electrical Characteristics, at T_j = 25 °C, unless otherwise specified

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Characteristics						
Transconductance	g_{fs}	$V_{DS}\geq 2*I_D*R_{DS(on)max}$, I_D=7A	-	8	-	S
Input capacitance	C_{iss}	V_{GS}=0V, V_{DS}=25V, f=1MHz	-	1200	-	pF
Output capacitance	C_{oss}		-	400	-	
Reverse transfer capacitance	C_{rss}		-	30	-	
Effective output capacitance,[5] energy related	$C_{o(er)}$	V_{GS}=0V, V_{DS}=0V to 400V	-	45	-	
Effective output capacitance,[6] time related	$C_{o(tr)}$		-	92	-	
Turn-on delay time	$t_{d(on)}$	V_{DD}=380V, V_{GS}=0/10V, I_D=11.6A, R_G=6.8Ω	-	10	-	ns
Rise time	t_r		-	8	-	
Turn-off delay time	$t_{d(off)}$		-	45	-	
Fall time	t_f		-	8	-	
Gate Charge Characteristics						
Gate to source charge	Q_{gs}	V_{DD}=400V, I_D=11.6A	-	5	-	nC
Gate to drain charge	Q_{gd}		-	26	-	
Gate charge total	Q_g	V_{DD}=400V, I_D=11.6A, V_{GS}=0 to 10V	-	49	-	
Gate plateau voltage	$V_{(plateau)}$	V_{DD}=400V, I_D=11.6A	-	5	-	V

[0] J-STD20 and JESD22

[1] Limited only by maximum temperature

[2] Repetitve avalanche causes additional power losses that can be calculated as $P_{AV}=E_{AR}*f$.

[3] Device on 40mm*40mm*1.5mm epoxy PCB FR4 with 6cm² (one layer, 70 µm thick) copper area for drain connection. PCB is vertical without blown air.

[4] Soldering temperature for TO-263: 220°C, reflow

[5] $C_{o(er)}$ is a fixed capacitance that gives the same stored energy as C_{oss} while V_{DS} is rising from 0 to 80% V_{DSS}.

[6] $C_{o(tr)}$ is a fixed capacitance that gives the same charging time as C_{oss} while V_{DS} is rising from 0 to 80% V_{DSS}.

[7] I_{SD}<=I_D, di/dt<=400A/us, V_{DClink}=400V, V_{peak}<$V_{BR, DSS}$, T_j<$T_{j,max}$.
Identical low-side and high-side switch.


Downloaded from Arrow.com.

Electrical Characteristics

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Inverse diode continuous forward current	I_S	T_C=25°C	-	-	11.6	A
Inverse diode direct current, pulsed	I_{SM}		-	-	34.8	
Inverse diode forward voltage	V_{SD}	V_{GS}=0V, I_F=I_S	-	1	1.2	V
Reverse recovery time	t_{rr}	V_R=400V, I_F=I_S , di_F/dt=100A/µs	-	380	-	ns
Reverse recovery charge	Q_{rr}		-	5.5	-	µC
Peak reverse recovery current	I_{rrm}		-	38	-	A
Peak rate of fall of reverse recovery current	di_{rr}/dt	T_j=25°C	-	1100	-	A/µs

Typical Transient Thermal Characteristics


Symbol	Value		Unit	Symbol	Value		Unit
	SPP_I	SPA			SPP_I	SPA	
R_{th1}	0.015	0.15	K/W	C_{th1}	0.0001878	0.0001878	Ws/K
R_{th2}	0.03	0.03		C_{th2}	0.0007106	0.0007106	
R_{th3}	0.056	0.056		C_{th3}	0.000988	0.000988	
R_{th4}	0.197	0.194		C_{th4}	0.002791	0.002791	
R_{th5}	0.216	0.413		C_{th5}	0.007285	0.007401	
R_{th6}	0.083	2.522		C_{th6}	0.063	0.412	



Downloaded from Arrow.com.


1 Power dissipation

$P_{tot} = f(T_C)$



2 Power dissipation FullPAK


$P_{tot} = f(T_C)$



3 Safe operating area

$I_D = f(V_{DS})$


parameter : $D = 0$, T_C=25°C



4 Safe operating area FullPAK

$I_D = f(V_{DS})$

parameter: $D = 0$, $T_C = 25°C$




Downloaded from Arrow.com.

5 Transient thermal impedance

$Z_{thJC} = f(t_p)$


parameter: $D = t_p/T$



6 Transient thermal impedance FullPAK

$Z_{thJC} = f(t_p)$


parameter: $D = t_p/t$



7 Typ. output characteristic

$I_D = f(V_{DS})$; T_j=25°C


parameter: t_p = 10 µs, V_{GS}



8 Typ. output characteristic

$I_D = f(V_{DS})$; T_j=150°C

parameter: t_p = 10 µs, V_{GS}




Downloaded from Arrow.com.

9 Typ. drain-source on resistance

$R_{DS(on)}=f(I_D)$


parameter: T_j=150°C, V_{GS}



10 Drain-source on-state resistance

$R_{DS(on)} = f\,(T_j)$


parameter : I_D = 7 A, V_{GS} = 10 V



11 Typ. transfer characteristics

$I_D= f\,(\,V_{GS}\,)$; $V_{DS}\geq 2$ x I_D x $R_{DS(on)max}$


parameter: t_p = 10 µs



12 Typ. gate charge

$V_{GS} = f\ (Q_{Gate})$

parameter: I_D = 11.6 A pulsed




Downloaded from Arrow.com.

13 Forward characteristics of body diode

$I_F = f(V_{SD})$


parameter: T_j , tp = 10 µs



14 Avalanche SOA

$I_{AR} = f(t_{AR})$


par.: $T_j \leq 150$ °C



15 Avalanche energy


$E_{AS} = f(T_j)$

par.: I_D = 5.5 A, V_{DD} = 50 V



16 Drain-source breakdown voltage

$V_{(BR)DSS} = f(T_j)$




Downloaded from Arrow.com.

17 Avalanche power losses

$P_{AR} = f(f)$


parameter: E_{AR}=0.6mJ



18 Typ. capacitances


$C = f(V_{DS})$

parameter: V_{GS}=0V, f=1 MHz




19 Typ. C_{oss} stored energy

$E_{oss}=f(V_{DS})$




Downloaded from Arrow.com.

Definition of diodes switching characteristics



Downloaded from Arrow.com.

PG-TO-220-3-1, PG-TO220-3-21



DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	4.30	4.57	0.169	0.180
A1	1.17	1.40	0.046	0.055
A2	2.15	2.72	0.085	0.107
b	0.65	0.86	0.026	0.034
b1	0.95	1.40	0.037	0.055
b2	0.95	1.15	0.037	0.045
b3	0.65	1.15	0.026	0.045
c	0.33	0.60	0.013	0.024
D	14.81	15.95	0.583	0.628
D1	8.51	9.45	0.335	0.372
D2	12.19	13.10	0.480	0.516
E	9.70	10.36	0.382	0.408
E1	6.50	8.60	0.256	0.339
e	2.54		0.100	
e1	5.08		0.200	
N	3		3	
H1	5.90	6.90	0.232	0.272
L	13.00	14.00	0.512	0.551
L1	-	4.80	-	0.189
øP	3.60	3.89	0.142	0.153
Q	2.60	3.00	0.102	0.118

DOCUMENT NO.
Z8B00003318

SCALE
0
2.5
0 2.5
5mm


EUROPEAN PROJECTION

ISSUE DATE
23-08-2007

REVISION
05

Downloaded from Arrow.com.

PG-TO220-3-31/3-111 Fully isolated package (2500VAC; 1 minute)




DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	4.55	4.85	0.179	0.191
A1	2.55	2.85	0.100	0.112
A2	2.42	2.72	0.095	0.107
b	0.65	0.85	0.026	0.033
b1	0.95	1.33	0.037	0.052
b2	0.95	1.51	0.037	0.059
b3	0.65	1.33	0.026	0.052
b4	0.65	1.51	0.026	0.059
c	0.40	0.63	0.016	0.025
D	15.85	16.15	0.624	0.636
D1	9.53	9.83	0.375	0.387
E	10.35	10.65	0.407	0.419
e	2.54		0.100	
e1	5.08		0.200	
N	3		3	
H	29.45	29.75	1.159	1.171
L	13.45	13.75	0.530	0.541
L1	3.15	3.45	0.124	0.136
øP	2.95	3.20	0.116	0.126
Q	3.15	3.50	0.124	0.138

REFERENCE	../..
SCALE	0, 2.5, 0, 2.5, 5mm
EUROPEAN PROJECTION	
ISSUE DATE	08-01-2007
FILE	TO220_2

Downloaded from Arrow.com.

PG-TO262-3-1, PG-TO262-3-21 (I²-PAK)



DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	4.300	4.572	0.169	0.180
A1	2.150	2.718	0.085	0.107
b	0.650	0.864	0.026	0.034
b1	0.635	1.400	0.025	0.055
c	0.330	0.600	0.013	0.024
c1	1.170	1.400	0.046	0.055
D	8.509	9.450	0.335	0.372
D1	6.900	-	0.272	-
E	9.700	10.363	0.382	0.408
E1	6.500	8.600	0.256	0.339
e	2.540		0.100	
e1	5.080		0.200	
N	3		3	
L	13.000	14.000	0.512	0.551
L1	-	4.800	-	0.189
L2	-	1.727	-	0.068

REFERENCE	JEDEC TO262
	0 2.5 5mm
EUROPEAN PROJECTION	
ISSUE DATE	05-05-2006
FILE	TO262_1

Downloaded from Arrow.com.

Published by
Infineon Technologies AG
81726 Munich, Germany
© 2007 Infineon Technologies AG
All Rights Reserved.

Legal Disclaimer
The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information
For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

Warnings
Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.
Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

Downloaded from Arrow.com.