
2007794-1 Product Details



Active

Impact High Density Backplane Connectors

IMP100,S,H,V3P16C,LG,REW46

2007794-1

TE Internal Number: 2007794-1

Pricing & Availability
Request Sample
Add to My Part List
Buy Product through Distributor

Product Highlights View All

- Connector Style = Header
- 96/Signal, 48/Ground
- 144 Positions
- Header Type = Fully Shrouded
- Board-to-Board Configuration = Right Angle, Vertical

Documents | Features | Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features

PCB Mount Retention Type	Action/Compliant Tail and Screw(s)
PCB Mount Alignment Type	Locating Post(s)

Electrical Characteristics

Impedance (Ω)	100
Operating Voltage Reference	AC/DC
Operating Voltage (VAC)	120
Operating Voltage (VDC)	120

Dimensions

Tail Length (mm [in])	1.2 [0.047]
Length (X-Axis) (mm [in])	38.30 [1.508]
Width (Z-Axis) (mm [in])	16.70 [0.657]
Profile Height (Y-Axis) (mm [in])	11.95 [0.470]
PCB Hole Diameter (mm [in])	0.46 [0.018]

Body Features

Header Type	Fully Shrouded

Contact Features

Contact Type	Pin
Contact Length (mm [in])	4.50 [0.177]
Contact Plating, Termination Area, Material	Matte Tin
Contact Plating, Termination Area, Thickness (µm [µin])	1.27 [50]
Contact Base Material	Copper-Nickel-Silicon
Underplate Material	Nickel
Underplate Material Thickness (µm [µin])	1.27 [50.000]

Housing Features

Connector Style	Header
End Wall Location	Right
Housing Color	Black
Housing Material	LCP (Liquid Crystal Polymer)

Configuration Features

Connector Contact Configuration (No. of Pos./Type)	96/Signal, 48/Ground
Number of Positions	144
Number of Differential Pairs Per Column	3
Number of Columns	16
Number of Rows	9
Shrouded	Yes
Guide Location	Left
Tail Orientation	In-line

Industry Standards

RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant
UL Rating	Recognized
UL File Number	E28476
UL Flammability Rating	UL 94V-0
CSA Certified	Yes

Environmental

Operating Temperature (°C [°F])	-55 – +85 [-67 – +185]

Conditions for Usage

Board-to-Board Configuration	Right Angle, Vertical

Operation/Application

Industry Application	Networking (Communications)

Packaging Features

Packaging Method	Tube/Box

Other

Brand	TE Connectivity

Related Products

Not quite the product you're looking for?
Find Similar Products

View Part in Product Feature Selector

Check for Tooling

© 2014 TE Connectivity Ltd. family of companies. All Rights Reserved

[+] Provide Website Feedback

[+] Feedback

Downloaded from Arrow.com.