


THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

NOTES:

- SPECIFICATION:
JACKET: PVC. MULTI-LAYER, 1ST LAYER WHITE; 2ND LAYER "COLOR"
OD: .106±.008 (2.7 mm)
CONDUCTOR: BARE COPPER, STRANDING 130 x 0.07 mm = 0.50 mm², 20 AWG.
- RATING:
VOLTAGE: 1,000 V CAT IV PER IEC 61010-031
CURRENT: 10 A MAX.
TEMPERATURE: -20° C TO +80° C.
- AVAILABLE IN 3 STANDARD LENGTHS AND 6 COLORS - SEE MODEL NUMBER BELOW.

| REVISIONS | | | |
|-----------|-----------------------------|---------|----------|
| REV. | DESCRIPTIONS | DATE | APPROVED |
| - | CLASS A RELEASED | 7/11/99 | |
| A | UPDATED FORMAT w/ CAGE CODE | 4/18/04 | |



MODEL NUMBER

CT2879-#-XXX

COLOR: 0 - BLACK
2 - RED
4 - YELLOW
5 - GREEN
6 - BLUE
9 - WHITE

LENGTH: 10 - 10 m PACKAGE
50 - 50 m SPOOL
100 - 100 m SPOOL

| | | | | | | | | | |
|------------------------|--|--|--|-----------------|--|--|--|--|--|
| THIRD ANGLE PROJECTION | | UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ± 1/32 .XX ± .02 .XXX ± .005 DO NOT SCALE DRAWING | | CONTRACT NO. | | Cal Test Electronics 22820 Savi Ranch Parkway Yorba Linda, CA 92887-4610 | | | |
| | | MATERIAL | | APPROVALS | | DATE | | TITLE WIRE, TEST LEAD, PVC JACKET, 0.50 mm², 20 AWG, 10 A | |
| | | | | DRAWN WDH | | 7/11/99 | | | |
| | | | | CHECKED | | | | | |
| | | | | ENGR. | | | | | |
| NEXT ASSY | | USED ON | | DESIGN ACTIVITY | | | | | |
| APPLICATION | | | | | | | | | |
| | | | | | | SIZE A | | CAGE CODE 43F45 | |
| | | | | | | DWG. NO. P287900 | | REV. A | |
| | | | | | | SCALE NONE | | SHEET 1 OF 1 | |