




Color: ■ black metallic

The configurable 852-1305 Industrial ETHERNET Switch is equipped with eight 10/100/1000BASE-T ports and four 1000BASE-SX/LX SFP slots (SFP modules are available as an option).

Packaged in a rugged housing, this switch offers both a redundant power supply and relay-based function monitoring. These functions, along with extensive ETHERNET switch options, make it ideal for a wide range of applications.

Features:

- Web-based/SNMP Management
- Redundant DC power supply
- Wide supply voltage range: 12 ... 60 VDC
- DIP switch to set alarm functions
- Fully compatible with IEEE 802.3, 802.3u, 802.3z, 802.3x, 802.3ad, 802.3ab, 802.1d, 802.1q, 802.1p, 802.1w and 802.1x standards
- Xpress Ring (redundant ring, recovery < 50 ms)
- Non-blocking, store-and-forward switching, rapid spanning tree protocol (RSTP)
- Autonegotiation at all 10/100/1000BASE-T ports
- Auto-MDI/MDIX (crossover) at all 10/100/1000BASE-T ports
- VLAN (802.1q) VID
- IGMP snooping for multicast filtering
- Port configuration, status, statistics
- Port trunking
- SNMP v1/v2 and RMON

Technical data	
Switching mode	Store-and-forward; non-blocking
Number of 1 Gb/s ports	8
Number of 1 Gb/s ports SFP	4
Communication standards	IEEE 802.3 10BASE-T IEEE 802.3u 100BASE-TX IEEE 802.3ab 1000BASE-T IEEE 802.3z 1000BASE-SX/LX IEEE 802.3x Flow Control IEEE 802.1w Rapid Spanning Tree Protocol (RSTP) IEEE 802.1Q VLAN Tagging IEEE 802.1ab Link Layer Discovery Protocol (LLDP) IEEE 802.1p Prioritization IEEE 802.1X Port Authentication ITU-T G8032v1/v2 Ethernet Ring Protection Switching (ERPS)
Redundancy function	Redundant DC power supply; STP; RSTP; MSTP; Jet Ring < 300 ms; Xpress Ring < 20 ms; Dual Homing < 20 ms; Dual Ring; ERPSv2 < 50 ms; LACP
Configuration options	DIP switch for signal contact Command Line Interface SNMPv1/v2c/v3



Technical data	
Diagnostics	Signal contact, Modbus/TCP, port status, port statistics, port load, traffic monitor, SFP information, syslog, mail alarm, SNMP traps Alarm contact; Alarm relay; NO; 1 A at 24 VDC
MAC table (size)	16000 addresses
Jumbo frame size	10000 bytes
Supply voltage	12 ... 60 VDC; 24 VDC (DNV GL); 24, 48 VDC (LR); Cable length <3 m
Power consumption (max.)	18 W
Current consumption (max.)	1500 mA
ESD (contact/air discharge)	8 kV / 15 kV
Transmission rate	Copper cable: 10/1000 Mbit/s; Fiber optic:1000 Mbit/s
Transmission medium (communication/fieldbus)	Copper cable: Cat. 5 or higher, 100 m maximum cable length; Fiber optic: SX Multi-Mode, LX Single-Mode
Optical fiber type	Single-mode and multi-mode
VLAN	Port-based and tag-based (4k VIDs)
Control Elements	14 x DIP switches: alarm function for supply voltages and ports 1 ... 12; 1 x reset button: system restart
Indicators	Device: LED (PWR, RPS, POST) green: power supply (primary), redundant power supply (secondary), POST function; LED (ALM) red: Alarm; LED (SFP) green, Status fiber optic ports; per port: LED (100, LNK/ACT) green: Status 100 Mbps, LNK/ACT ports 1 ... 8

Connection Data	
Connection technology: communication/fieldbus	Copper cable: 8 x RJ-45; Fiber optic: 4 x SFP slots (e.g., with SFP module and LC fiber-optic connector)
Connection technology: supply	1 x Built-in male connector: 231-436/001-000; included female connector (MCS Connectors): 2231-106/026-000
Connection technology: device configuration	1 x RS-232 serial interface

Physical data	
Width	50 mm / 1.969 inches
Height	162 mm / 6.378 inches
Depth	120 mm / 4.724 inches

Mechanical data	
Mounting type	DIN-35 rail

Material data	
Color	black metallic
Housing material	Aluminum
Fire load	0.2 MJ
Weight	910 g
Conformity marking	CE

Environmental requirements	
Ambient temperature (operation)	-40 ... +70 °C (-40 ... +70 °C (CE); -25 ... +70 °C (DNV GL); +5 ... +70 °C (LR))
Ambient temperature (storage)	-40 ... +80 °C
Protection type	IP30
Note on protection type	Use per UL 61010: Indoor
Pollution degree	2 per UL 61010
Relative humidity (without condensation)	95 %
Vibration resistance	Per IEC 60068-2-6
Shock resistance	per IEC 60068-2-27
EMC immunity to interference	per EN 61000-6-2
EMC emission of interference	per EN 61000-6-4

Data Act		
Pre-contractual Information		Data-Act-AUT-Products-Switches

Commercial data		
PU (SPU)		1 pcs
Packaging type		Box
Country of origin		TW
GTIN		4055143327169
Customs tariff number		85176200000

Product Classification		
UNSPSC		43222612
eCl@ss 10.0		19-17-01-30
eCl@ss 9.0		19-17-01-06
ETIM 9.0		EC000734
ETIM 10.0		EC000734
ECCN		5A992.C

Environmental Product Compliance		
RoHS Compliance Status		Compliant,No Exemption

Approvals / Certificates								
General approvals		Declarations of conformity and manufacturer's declarations						
								
Approval	Standard	Certificate Name						
KC National Radio Research Agency	Article 58-2, Clause 3	MSIP-REM-W43-ISW852						
		<table><tr><th>Approval</th><th>Standard</th><th>Certificate Name</th></tr><tr><td>EU-Declaration of Conformity WAGO GmbH & Co. KG</td><td>-</td><td>-</td></tr></table>	Approval	Standard	Certificate Name	EU-Declaration of Conformity WAGO GmbH & Co. KG	-	-
Approval	Standard	Certificate Name						
EU-Declaration of Conformity WAGO GmbH & Co. KG	-	-						

Approvals for marine applications		
		
Approval	Standard	Certificate Name
DNV DNV GL SE	-	TAA0000239

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 852-1305

↓

Documentation

Manual

Product Manual 8-Port 1000BASE-T + 4-Slot 1000BASE-SX/LX Industrial Switch

V 1.3.1
18.01.2022

pdf
14717.13 KB

↓

System Description

Industrial Switches – General Product Information

pdf
1873.93 KB

↓

Bid Text			
852-1305	09.05.2018	docx 18.65 KB	↓
852-1305	19.02.2019	xml 6.27 KB	↓

CAD/CAE-Data

CAD data

2D/3D Models 852-1305

↓

CAE data

EPLAN Data Portal 852-1305

↓

WSCAD Universe 852-1305

↓

ZUKEN Portal 852-1305

↓

Runtime Software

Firmware

0852-1305, Industrial-Managed-Switch

V 14
27.02.2024

zip
10221.60 KB

↓



1 Compatible Products

1.1 Optional Accessories

1.1.1 Cables and connectors

1.1.1.1 Connector plug



Item No.: 750-979/000-011
Connector ETHERNET; RJ-45; Cat. 6A; angled; Code T568A; AWG 22; Strain relief



Item No.: 750-979/000-021
Connector ETHERNET; RJ-45; Cat. 6A; angled; Code T568A; AWG 24; Strain relief



Item No.: 750-979/000-012
Connector ETHERNET; RJ-45; Cat. 6A; angled; Code T568B; AWG 22; Strain relief



Item No.: 750-979/000-022
Connector ETHERNET; RJ-45; Cat. 6A; angled; Code T568B; AWG 24; Strain relief



Item No.: 750-977/000-011
Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568A; AWG 22



Item No.: 750-978/000-011
Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568A; AWG 22; Strain relief



Item No.: 750-977/000-021
Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568A; AWG 24



Item No.: 750-978/000-021
Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568A; AWG 24; Strain relief



Item No.: 750-977/000-012
Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568B; AWG 22



Item No.: 750-978/000-012
Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568B; AWG 22; Strain relief



Item No.: 750-977/000-022
Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568B; AWG 24



Item No.: 750-978/000-022
Connector ETHERNET; RJ-45; Cat. 6A; straight; Code T568B; AWG 24; Strain relief



Item No.: 750-979/000-013
Connector PROFINET; RJ-45; Cat. 6A; angled; AWG 22; Strain relief



Item No.: 750-977/000-013
Connector PROFINET; RJ-45; Cat. 6A; straight; AWG 22



Item No.: 750-978/000-013
Connector PROFINET; RJ-45; Cat. 6A; straight; AWG 22; Strain relief



Item No.: 750-975
ETHERNET RJ-45 connector, IP20; ETHERNET 10/100 Mbit/s; for field assembly



Item No.: 750-976
PROFINET RJ-45 connector, IP20; ETHERNET 10/100 Mbit/s; for field assembly

1.1.2 Interface module

1.1.2.1 Interface module



Item No.: 289-195
Interface module; RJ-45; IDC technology; Cat. 6; in mounting carrier; with shield connection



Item No.: 289-175
Interface module; RJ-45; PCB terminal blocks, double-row; Cat. 5; in mounting carrier; with shield connection; with shield clamping saddle; 1,50 mm²



Item No.: 289-172
Interface module; RJ-45; RJ-45; Cat. 5; in mounting carrier



Item No.: 289-196
Interface module; RJ-45; with power jumper contacts; PCB terminal blocks; Cat. 5

1.1.3 Plug

1.1.3.1 SFP module



Item No.: 852-1210
SFP Module 1000BASE; LX Single-Mode 1310 nm LC; 10 km; Extended temperature range; Digital Diagnostics Monitoring; silver-colored



Item No.: 852-1200
SFP Module 1000BASE; SX Multi-Mode 850 nm LC; 0.55 km; Extended temperature range; Digital Diagnostics Monitoring; silver-colored



Item No.: 852-1280
SFP Module 1000BASE; ZX Single-Mode 1550 nm LC; 80 km; Extended temperature range; Digital Diagnostics Monitoring; silver-colored

1.1.4 Power supply

1.1.4.1 Power Supply

			
Item No.: 787-1602 Switched-mode power supply; Classic; 1-phase; 24 VDC output voltage; 1 A output current; NEC Class 2; DC OK signal	Item No.: 787-1632 Switched-mode power supply; Classic; 1-phase; 24 VDC output voltage; 10 A output current; TopBoost; DC OK contact	Item No.: 787-1606 Switched-mode power supply; Classic; 1-phase; 24 VDC output voltage; 2 A output current; NEC Class 2; DC OK signal	Item No.: 787-1622 Switched-mode power supply; Classic; 1-phase; 24 VDC output voltage; 5 A output current; TopBoost; DC OK contact
			
Item No.: 787-1635 Switched-mode power supply; Classic; 1-phase; 48 VDC output voltage; 10 A output current; TopBoost; DC OK contact	Item No.: 787-1623 Switched-mode power supply; Classic; 1-phase; 48 VDC output voltage; 2 A output current; DC OK signal	Item No.: 787-1633 Switched-mode power supply; Classic; 1-phase; 48 VDC output voltage; 5 A output current; TopBoost; DC OK contact	