






REV.	DATE	ECR NO.	DESCRIPTION
A	01/26/00	—	UPDATE DRAWING FORMAT
B	05/02/07	—	REVISE BARREL AND FERRULE DIMENSIONS
C	01/12/09	—	REVISE CABLE CALL OUT IN PART DESCRIPTION.



RECOMMENDED
CABLE STRIPPING DIM'S



NOTE:

1. CRIMPED FERRULE HEX CRIMP SIZE .128" [3.25]
2. CONTACT PIN TO SOLDER.

				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex							
8					DRAWN	G.R.S.	01/12/09									
7					CHECKED											
6					ISSUED			PART DESCRIPTION								
5	HEAT SHRINK TUBE		BLACK		1	SHEET			MINI SMB CRIMP PLUG – 75 ohm (FOR RG-179/187 CABLE)							
4	FERRULE	COPPER	NICKEL		1	1 OF 1			PART NO.							
3	CONTACT PIN	BER. COPPER	GOLD		1				142178-75							
2	INSULATOR	PTFE	NATURAL		1	CAD FILE			DWG. NO.							
1	BODY	BRASS	NICKEL		1	C:/142/142178-75.DWG			142178-75.DWG		REV.	C	SIZE	A	SCALE	NA
	DESCRIPTION	MATERIAL	FINISH		QTY											