


THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.

NOTES:


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
^		A20		REVISED PER ECR-20-016246	07DEC2020	MM	JL
		A21		REVISED PER ECR-21-110497	17AUG2021	JL	MM
		B		REVISED PER ECR-21-118984	11NOV2021	SD	MM
		B1		REVISED PER ECR-22-127557	24JAN2022	SD	MM

1. MATERIALS:
HOUSING: GLASS-FILLED THERMOPLASTIC, UL 94V-0 RATED DIMMING CONTACTS (2 OR 4) AND LINE VOLTAGE CONTACTS (3): COPPER ALLOY
2. FINISH:
DIMMING CONTACTS (2 OR 4): NICKEL UNDERPLATE ENTIRE CONTACT 0.127 μm MIN THICK. GOLD PLATE CONTACT PAD AREA (MATING FACE SIDE ONLY) 0.76 μm MIN THICK. MATTE TIN PLATE TAB ON BOTH SIDES 0.30 μm MIN THICK. LINE VOLTAGE CONTACTS (3): TIN PLATE.
3. LINE VOLTAGE CONDUCTORS (3):
14 AWG, 600V, 150°C RATED, COPPER 41/30 STRANDED PER UL STYLE AWM 3321.
4. MATING INTERFACE PER ANSI C136.41-2013.
5. OPTIONAL DIMMING CONTACTS (2) SUPPLIED.
6. DIMMING CONDUCTORS (2 OR 4):
18 AWG, 600V, 150°C RATED, 16/30 STRANDED, PER UL STYLE AWM 3321.
7. LINE VOLTAGE CONDUCTORS (3):
14 AWG, 600V, 105°C RATED, COPPER 41/30 STRANDED. PER UL STYLE AWM 1015.

8. DIMMING CONDUCTORS (2 OR 4):
18 AWG, 600V, 105°C RATED, COPPER 16/30 STRANDED
PER UL STYLE AWM 1015.
9. PRELIMINARY.
10. FOR PART NUMBER 5-2213362-4 ONLY,
STRIP AND REMOVE INSULATION AS SHOWN.
LEAD WIRES TO BE SOLDER DIPPED.
11. MUST BE USED WITH EITHER GASKET P/N 2213469-1
OR P/N 2324246-1 (SOLD SEPARATELY).





SEE SHEET 2 FOR
WIRING COLOR CODE




12.0	203.0	153.0	153.0	7 AND 8	4 5	9-2213362-4
12.7	1036.3	1000	986.5	7 AND 8	4 5	8-2213362-4 9
12.7	266.3	230.0	216.5	7 AND 8	4 5	7-2213362-4
12.7	236.3	200.0	-	7	-	6-2213362-4 9
12.7	341.1	304.8	-	3	-	6-2213362-2
12.7	341.1	304.8	-	7	-	6-2213362-1
15.88	264.9	228.6	-	3	-	5-2213362-9
BLACK WIRE:15.88 WHITE WIRE:15.88 RED WIRE:6.35	798.3	762.0	-	3	-	5-2213362-8
9.0	341.1	304.8	291.3	7 AND 8	4 5	5-2213362-4 10 9
9.0	211.3	175.0	175.0	7 AND 8	4 5	4-2213362-6
9.0	341.1	304.8	291.3	7 AND 8	4	4-2213362-5
12.7	950.7	914.4	914.4	7 AND 8	4 5	4-2213362-4 9
8.0	73.0	35.0	35.0	7 AND 8	4 5	3-2213362-4 9
12.7	1865.1	1828.8	1815.3	3 AND 6	2	3-2213362-1 9
12.7	736.3	700.0	686.5	7 AND 8	4 5	2-2213362-4
12.7	696.3	660.0	646.5	3 AND 6	4 5	2-2213362-2 9
12.7	696.3	660.0	646.5	3 AND 6	2	2-2213362-1
12.7	536.3	500.0	486.5	7 AND 8	4 5	1-2213362-4
12.7	536.3	500.0	486.5	7 AND 8	2	1-2213362-3 9
12.7	1823.3	1346.0	1332.5	3 AND 6	4 5	1-2213362-2
12.7	536.3	500.0	486.5	3 AND 6	2	1-2213362-1 9
12.7	341.1	304.8	291.3	7 AND 8	4 5	2213362-4
12.7	341.1	304.8	291.3	7 AND 8	2	2213362-3
12.7	341.1	304.8	291.3	3 AND 6	4 5	2213362-2
12.7	341.1	304.8	291.3	3 AND 6	2	2213362-1
D	C	A	B	WIRE STYLE	QUANTITY OF DIMMING CONTACTS	PART NO.
STRIP LENGTH	OVERALL LENGTH	WIRE LENGTH				

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SHAFFER	26JUN2013				TE Connectivity							
		CHK E. HOWARD	26JUN2013											
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD E. HOWARD	26JUN2013		NAME							
		0 PLC ±·		PRODUCT SPEC 108-32059		RECEPTACLE ASSEMBLY, DIMMABLE PHOTOCONTROL -								
		1 PLC ±·												
		2 PLC ±0.13												
		3 PLC ±·		APPLICATION SPEC 114-32115		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO				
		4 PLC ±·				A200779		C=2213362						
MATERIAL		FINISH		WEIGHT		-				-				
-		-		-		CUSTOMER DRAWING		SCALE		1:1	SHEET	1 OF 2	REV	B1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SHAFFER	26 JUN 2013		 TE Connectivity					
		CHK E. HOWARD	26 JUN 2013							
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD E. HOWARD	26 JUN 2013		NAME	RECEPTACLE ASSEMBLY, DIMMABLE PHOTOCONTROL -			
	0 PLC ±-		PRODUCT SPEC							
	1 PLC ±-		108-32059							
	2 PLC ±0.13		APPLICATION SPEC							
	3 PLC ±-		114-32115		SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO	
MATERIAL	FINISH		WEIGHT		A200779		C-2213362		-	
			CUSTOMER DRAWING			SCALE	1:1		SHEET 2 OF 2	REV B1