



SERIES: MD-SV

|


DESCRIPTION: MINI DIN CONNECTOR

FEATURES

- PCB mount
- vertical mount
- 3~8 pins



PART NUMBER KEY




SPECIFICATIONS

parameter	conditions/description	min	typ	max	units
rated input voltage			100 12		Vac Vdc
rated input current	at 100 Vac at 12 Vdc			1 2	A A
contact resistance				30	mΩ
insulation resistance	at 250 Vdc	50			MΩ
voltage withstand	for 1 minute			250	Vac
insertion force		0.8		6.0	kg
withdrawal force		0.8		4.5	kg
operating temperature		-20		85	°C
life			1,000		cycles
flammability rating	UL94V-0				
RoHS	yes				

MECHANICAL DRAWINGS (MD-30SV, MD-40SV, MD-50SV)


units: mm
tolerance: ±0.3 mm
PCB: ±0.1 mm
unless otherwise noted

ITEM	DESCRIPTION	MATERIAL	PLATING/COLOR
1	body	PBT [UL94V-0]	black
2	earth terminal	brass	tin
3	terminals	phosphor bronze	silver




A-A


MD-30SV




MD-40SV




MD-50SV




Recommended PCB Layout
Bottom View
(Date Codes prior to 03/03/2022)




Recommended PCB Layout
Bottom View
(Date Codes after 03/03/2022)




Recommended PCB Layout
Bottom View
(Date Codes prior to 03/03/2022)



Recommended PCB Layout
Bottom View
(Date Codes after 03/03/2022)



Recommended PCB Layout
Bottom View
(Date Codes prior to 03/03/2022)




Recommended PCB Layout
Bottom View
(Date Codes after 03/03/2022)

MECHANICAL DRAWINGS (MD-60SV, MD-70SV, MD-80SV)

units: mm
tolerance: ±0.3 mm
PCB: ±0.1 mm
unless otherwise noted


ITEM	DESCRIPTION	MATERIAL	PLATING/COLOR
1	body	PBT [UL94V-0]	black
2	earth terminal	brass	tin
3	terminals	phosphor bronze	silver




MD-60SV

MD-70SV


MD-80SV




Recommended PCB Layout
Bottom View
(Date Codes prior to 03/03/2022)




Recommended PCB Layout
Bottom View
(Date Codes prior to 03/03/2022)




Recommended PCB Layout
Bottom View
(Date Codes prior to 03/03/2022)



Recommended PCB Layout
Bottom View
(Date Codes after 03/03/2022)



Recommended PCB Layout
Bottom View
(Date Codes after 03/03/2022)



Recommended PCB Layout
Bottom View
(Date Codes after 03/03/2022)

REVISION HISTORY

rev.	description	date
1.0	initial release	02/23/2006
1.01	new template applied	03/07/2012
1.02	updated datasheet	08/25/2017
1.03	updated housing, added 7 pin version, brand update	10/08/2019
1.04	modified design, changed factory	02/18/2022
1.05	logo, datasheet style update	08/05/2022
1.06	CUI Devices rebranded to Same Sky	09/12/2024

The revision history provided is for informational purposes only and is believed to be accurate.



Same Sky offers a one (1) year limited warranty. Complete warranty information is listed on our website.

Same Sky reserves the right to make changes to the product at any time without notice. Information provided by Same Sky is believed to be accurate and reliable. However, no responsibility is assumed by Same Sky for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

Same Sky products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

sameskydevices.com