

**Part Number :** [935990012](#)


**Product Description :** Heavy Duty Connector S-QD 8-Pole Single-Ended Cordset, Male (90°) to Pigtail, 14 AWG, Black TPE Cable, 25.0m (82.02') Length

**Series Number :** 93599

**Status :** Active

**Product Category :** Circular Industrial Cordsets

**Engineering Part Number :** 93599-0005-M250



---

## Documents and Resources

### Drawings

[935990012\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

[CE - Declaration of Conformity](#)

[UKCA - Declaration of Conformity](#)

## Part Details

### General

Status	Active
Category	Circular Industrial Cordsets
Series	93599
Description	Heavy Duty Connector S-QD 8-Pole Single-Ended Cordset, Male (90°) to Pigtail, 14 AWG, Black TPE Cable, 25.0m (82.02') Length
IP Rating	IP67
Product Name	Heavy-Duty Connectors
Type	Single Ended
UPC	78172551928

### Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	600V

### Physical

Cable Diameter	9.47mm (.373")
Cable Length	25.0m (82.02')
Color - Cable Jacket	Black
Connector End A	HDC
Connector End B	Pigtail
Coupling Style	Latching
Gender	Male-Pigtail
Keyway	Single
LED Indicator	None
Material - Cable Jacket	TPE

Material - Connector Body	Polyamide
Material - Contact	Copper Alloy
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	652.000/g
Orientation	90° to Pigtail
Poles	8
Temperature Range - Operating	-40° to +90°C
Wire/Cable Type	TC-ER
Wire Size (AWG)	14

---

This document was generated on May 20, 2026