



Pushing Performance
Since 1945

M12 D-Coded gender changer



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 381 6401
Specification	M12 D-Coded gender changer
HARTING eCatalogue	https://harting.com/21033816401

Identification

Category	Accessories
Series	Circular connectors M12
Connector 1	M12 D-coding
	Female
	4 poles
Type of accessory	Gender changer
Description of the accessory	Panel feed through

Version

Gender	Female
Coding	D-coding

Technical characteristics

Rated current	4 A
Rated voltage	48 V AC
	60 V DC
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s
	100 Mbit/s
Limiting temperature	-40 ... +85 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition

Material properties

Material (insert)	Liquid crystal polymer (LCP)
-------------------	------------------------------



Pushing Performance
Since 1945

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
Material (hood/housing)	Zinc die-cast
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel
	Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

Specifications and approvals

Specifications	IEC 61076-2-101
UL / CSA	UL 2238 CYJV2.E302521
	CSA-C22.2 No. 182.3 CYJV8.E302521
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	55 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140138445
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943



Pushing Performance
Since 1945

Commercial data

UNSPSC 24.0	39121400
-------------	----------
