



PRODUCT NUMBER	PITCH
TYxx01x000J0G	5.00 mm



Material

- (a) Terminal body (metal housing): Brass (Cu Zn) Ni plated
- (b) Terminal screw: Steel Zinc plating "-" slot type
- (c) Wire guard: PhBz, tin plated
- (d) Terminal (housing): Thermoplastic (UL94V-0)

Electrical cULus TUV

- Voltage rating: 300VAC / 300VAC
- Current rating: 10A / 10A
- Wire range: 0.2-2.5mm²
- Solid wire (AWG): 14-26 / 14-26
- Stranded wire (AWG): 14-26 / 14-26
- Torque: 3.5Lb-In / 0.4Nm
- Screw: M2.6
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV / 2.5KV
- Operating temperature: -40°C to +115°C
- Safety Approval: 

PART NO.: TY xx 01 x 0 00J0 G

N=Number of poles
 Dim L=Nx5.0
 Dim B=(N-1)x5.0

poles	Tolerance
2-6p	±0.15
7-12p	±0.20
13-18p	±0.25
19-24p	±0.30

Solid block
 No. of poles
 02 2 poles
 03 3 poles

 24 24 poles

Color
 0 Black (RAL9005)
 2 Red (RAL3001/D)
 3 Orange (RAL2011/P)
 4 Yellow (RAL1018/A)
 5 Green (RAL6018/T)
 6 Blue (RAL5015/A)
 8 Grey (RAL7035/D)
 9 White (RAL1102)
 C Green (RAL6018/U)

RoHS compliant
 (lead<4%)
 In copper Alloy

mat'l. code				surface ASME Y14.5 ✓		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK					
ltr ecn no dr date				tolerances unless otherwise specified											
				angles		X.±0.5									
						X.X±0.3									
				X*±1°		X.XX±0.1									
				dr		EVIN ZHONG		041614							
				engr		EVIN ZHONG		041614							
				chr		HANKE FENG		041614							
				appd		SHI JUN		041614							
sheet index		revision sheet		A 1						dwg no		sheet 1 of 1		size	
										TYxx01x000J0G				A4	
										type		CUSTOMER Drawing			