



REPRESENTATIVE IMAGE

Product: [9842NH](#) 

RS485, 2 Pr #24 Str TC, PO Ins, OS+TC Brd, LSZH Jkt, Dca

Product Description

RS-485, 2 Pair 24AWG (7x32) Tinned Copper, PO Insulation, Overall Beldfoil®+Tinned Copper Braid(90%) Shield, LSZH Outer Jacket, CPR Dca

Technical Specifications

Product Overview

Suitable Applications:	RS-485, POS; Computer communications; Low Voltage Analog Signals (4-20ma, 0-10v, ...); Low Voltage Digital Control (24v, ...); Line Level Audio; Panel Wiring; serial communication (RS-485 standard) comprising of PLCs, VFDs, HMIs, motors, RTU, SCADA, etc. within noisy environments over long distance, etc.
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
24	7x32	TC - Tinned Copper	2

Conductor Count:	4
Total Number of Pairs:	2

Insulation

Material	Nominal Diameter	Diameter +/- Tolerance	Nominal Wall Thickness
PE - Polyethylene	1.73 mm	0.05 mm	0.02 in

Color Chart

Number	Color
Pair 1	White/Blue & Blue/White
Pair 2	White/Orange & Orange/White

Outer Shield

Type	Layer	Material	Material Trade Name	Coverage [%]	Thickness of Foil	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	1	Bi-Laminate (Alum+Poly)	Beldfoil® (Z-Fold®)	100%	9 / 23 µm	TC - Tinned Copper	AWG24/7	7x32
Braid	2	Tinned Copper (TC)		90%				

Outer Jacket

Material	Color	Nominal Diameter	Nominal Wall Thickness
LSZH - Low Smoke Zero Halogen (Flame Retardant)	Chrome (RAL 7037)	8.65 mm	0.9 mm

Construction and Dimensions

Stranding

Lay Direction	Twists
Left Hand	12 twist/ft

Cabling

Description	Filler
2 pairs and 2 fillers twisted to cable core	Polypropylene (2x) (White, 2.87 mm)

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
78.7 Ohm/km	7.2 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
42 pF/m	75.5 pF/m

Impedance

Frequency [MHz]	Nominal Characteristic Impedance
1	120 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	1.97 dB/100m

Delay

Max. Delay Skew	Nominal Delay	Nominal Velocity of Propagation (VP) [%]
66 ns/100m	1.54 ns/ft	66%

Current

Element	Max. Recommended Current [A]
Conductor(s)	2.1 Amps per Conductor

Voltage

Voltage Rating [V]
300 V

Temperature Range

Installation Temp Range:	-15°C To +80°C
Storage Temp Range:	-45°C To +80°C
Operating Temp Range:	-20°C To +80°C
Operating Temp Range (Flexible Install):	-15°C To +80°C
Operating Temp Range (Fixed Install):	-45°C To +80°C

Mechanical Characteristics

Oil Resistance:	IEC 60811-404
Bulk Cable Weight:	49 lbs/1000ft
Max. Pull Tension:	395 N
Min. Bend Radius During Installation:	86.5 mm
Min. Bend Radius/Minor Axis:	3.25 in

Standards

CPR Euroclass:	Dca-s2,d2,a1
CENELEC Compliance:	EN 50290-2-27

Applicable Environmental and Other Programs

Environmental Space:	Indoor - Euroclass Dca
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LS0H, Toxicity Testing

IEC Flammability:	IEC 60332-1-2 and IEC 60332-3-24
IEC 60754-1 - Halogen Amount:	Zero

IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity:	2.5 µS/mm
IEC 60754-2 - Halogen Acid Gas Amount - Min. pH:	4.3
IEC 61034-2 - Smoke Density Min. Transmittance:	60%

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Put-Up Type	Length	UPC/EAN
9842NH.02500	Black	Reel	500 m	8719605023308
9842NH.02520	Black	Reel	520 m	8719605172129
9842NH.021000	Black	Reel	1,000 m	8719605155405
9842NH.022500	Black	Reel	2,500 m	8719605023292
9842NH.00152	Chrome	Reel	152 m	8719605023230
9842NH.00305	Chrome	Reel	305 m	8719605023254
9842NH 060500	Chrome	Reel	500 ft	612825259572
9842NH.00500	Chrome	Reel	500 m	8719605023261
9842NH 0601000	Chrome	Reel	1,000 ft	612825259565
9842NH 0601000	Chrome	Reel	1,000 ft	612825259565
9842NH.001000	Chrome	Reel	1,000 m	8719605023223
9842NH.002500	Chrome	Reel	2,500 m	8719605023247
9842NH.01305	White	Reel	305 m	8719605023285
9842NH.01500	White	Reel	500 m	8719605184795
9842NH.011000	White	Reel	1,000 m	8719605023278

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.446 Revision Date: 11-04-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.