

**Part Number :** [731375013](#)

**Product Description :** BNC Jack, Right-Angle, Bulkhead Receptacle, PCB, Through Hole, White PBT Housing, Height 13.20mm, Nut and Lockwasher Included, Tin Plated Leads, 50 Ohms

**Series Number :** 73171

**Status :** Active

**Product Category :** RF / Coaxial Connectors



---

## Documents and Resources

### Drawings

[731375013 sd.pdf](#)

[STEP AP242](#)


[SOLIDWORKS](#)

[Creo](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### [Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

### [Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	RF / Coaxial Connectors
Series	73171
Description	BNC Jack, Right-Angle, Bulkhead Receptacle, PCB, Through Hole, White PBT Housing, Height 13.20mm, Nut and Lockwasher Included, Tin Plated Leads, 50 Ohms
Application	RF
Comments	13.20mm Profile
Product Name	BNC
Style	PCB
Type	Miniature
UPC	800753692060

### Agency

CSA	LR19980
UL	E107635

### Electrical

Frequency	2 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

## Physical

Cable Attachment	N/A
Flammability	94V-0
Gender	Jack
Keying to Mating Part	N/A
Net Weight	14.735/g
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	Yes
Panel Mount Method	Bulkhead
PCB Mounting	Through Hole
PCB Thickness - Recommended	3.20mm
Reverse Polar	No
Wire/Cable Type	N/A

## Solder Process Data

Max-Duration	10
Lead-Free Process Capability	WAVE
Max-Cycle	1
Max-Temp	245

---

This document was generated on Dec 31, 2025