Pushing Performance
Since 1945

Han-Eco cable gland M32



Image is for illustration purposes only. Please refer to product description.

Part number	19 41 000 5131
Specification	Han-Eco cable gland M32
HARTING eCatalogue	https://harting.com/19410005131

Identification

Category	Accessories
Series of hoods/housings	Han-Eco®
Type of accessory	Cable gland

Technical characteristics

Tightening torque	15 Nm Fitting 4 Nm Cap nut
Wrench size	36
Limiting temperature	-40 ... +125 °C
Size	M32
Clamping range	13 ... 21 mm

Material properties

Material (cable glands)	Polyamide (PA)
Colour (cable gland)	RAL 9005 (jet black)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

Material properties

Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Commercial data

Packaging size	2
Net weight	32.165 g
Country of origin	Germany
European customs tariff number	39174000
GTIN	5713140130524
eCl@ss	27140801 Screwed cable gland (electrical)
ETIM	EC000441
UNSPSC 24.0	39121431

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.