



Part Number : [496270382](#)
Product Description : 4.20mm Wire-to-Wire Lower
TPA for Female Housing, 3 Circuits, Blue
Series Number : 49627
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

[496270382_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[PK-49623-001-001.pdf](#)

[PS-49623-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	49627
Description	4.20mm Wire-to-Wire Lower TPA for Female Housing, 3 Circuits, Blue
Application	Power, Wire-to-Wire
Product Name	N/A
UPC	883906035716

Physical

Circuits Detail	3
Circuits (maximum)	3
Color - Resin	Blue
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.143/g
Number of Rows	1
Packaging Type	Bag

Panel Mount	No
Pitch - Mating Interface	4.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
4.20mm Wire-to-Wire TPA Connector for Female Housings	<u>49624</u>

This document was generated on Apr 30, 2026