

N-Channel Power MOSFET

800V, 12A, 400mΩ

FEATURES

- Super-Junction technology
- High performance, small $R_{DS(on)} \cdot Q_g$ figure of merit (FOM)
- High ruggedness performance
- 100% UIS and R_g tested
- Compliant to RoHS Directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21


KEY PERFORMANCE PARAMETERS		
PARAMETER	VALUE	UNIT
V_{DS}	800	V
$R_{DS(on)}$ (max)	400	mΩ
Q_g	51	nC

APPLICATIONS

- Power Supply
- AC/DC LED Lighting



ITO-220S



ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

PARAMETER	SYMBOL	LIMIT	UNIT
Drain-Source Voltage	V_{DS}	800	V
Gate-Source Voltage	V_{GS}	± 30	V
Continuous Drain Current (Note 1)	I_D	$T_C = 25^\circ\text{C}$	A
		$T_C = 100^\circ\text{C}$	A
Pulsed Drain Current (Note 2)	I_{DM}	48	A
Total Power Dissipation @ $T_C = 25^\circ\text{C}$	P_D	69	W
Single Pulse Avalanche Energy (Note 3)	E_{AS}	812	mJ
Single Pulse Avalanche Current (Note 3)	I_{AS}	5.7	A
Operating Junction and Storage Temperature Range	T_J, T_{STG}	- 55 to +150	$^\circ\text{C}$

THERMAL PERFORMANCE

PARAMETER	SYMBOL	LIMIT	UNIT
Junction to Case Thermal Resistance	$R_{\theta JC}$	1.8	$^\circ\text{C/W}$
Junction to Ambient Thermal Resistance	$R_{\theta JA}$	62	$^\circ\text{C/W}$

Thermal Performance Note: $R_{\theta JA}$ is the sum of the junction-to-case and case-to-ambient thermal resistances. The case-thermal reference is defined at the solder mounting surface of the drain pins. $R_{\theta JA}$ is guaranteed by design while $R_{\theta CA}$ is determined by the user's board design.

ELECTRICAL SPECIFICATIONS (T _A = 25°C unless otherwise noted)						
PARAMETER	CONDITIONS	SYMBOL	MIN	TYP	MAX	UNIT
Static ^(Note 4)						
Drain-Source Breakdown Voltage	V _{GS} = 0V, I _D = 250μA	BV _{DSS}	800	--	--	V
Gate Threshold Voltage	V _{DS} = V _{GS} , I _D = 250μA	V _{GS(TH)}	2	3.3	4	V
Gate Body Leakage	V _{GS} = ±30V, V _{DS} = 0V	I _{GSS}	--	--	±100	nA
Zero Gate Voltage Drain Current	V _{DS} = 800V, V _{GS} = 0V	I _{DSS}	--	--	1	μA
Drain-Source On-State Resistance	V _{GS} = 10V, I _D = 2.7A	R _{DS(on)}	--	300	400	mΩ
Dynamic ^(Note 5)						
Total Gate Charge	V _{DS} = 640V, I _D = 8A, V _{GS} = 10V	Q _g	--	51	--	nC
Gate-Source Charge		Q _{gs}	--	10	--	
Gate-Drain Charge		Q _{gd}	--	24	--	
Input Capacitance	V _{DS} = 100V, V _{GS} = 0V, f = 1.0MHz	C _{iss}	--	1848	--	pF
Output Capacitance		C _{oss}	--	90	--	
Gate Resistance	f = 1.0MHz	R _g	--	3.3	6.6	Ω
Switching ^(Note 6)						
Turn-On Delay Time	V _{DD} = 400V, I _D = 8A, V _{GS} = 10V, R _{GEN} = 5Ω	t _{d(on)}	--	19	--	ns
Turn-On Rise Time		t _r	--	26	--	
Turn-Off Delay Time		t _{d(off)}	--	57	--	
Turn-Off Fall Time		t _f	--	28	--	
Source-Drain Diode ^(Note 4)						
Body-Diode Continuous Forward Current		I _S	--	--	8	A
Body-Diode Pulsed Current		I _{SM}	--	--	32	A
Forward Voltage	I _S = 8A, V _{GS} = 0V	V _{SD}	--	--	1.4	V
Reverse Recovery Time	I _S = 8A	t _{rr}	--	340	--	ns
Reverse Recovery Charge	dl _F /dt = 100A/μs	Q _{rr}	--	4.9	--	μC

Notes:

- Current limited by package.
- Pulse width limited by the maximum junction temperature.
- $L = 50mH, I_{AS} = 5.7A, V_{DD} = 50V, R_G = 25\Omega$, Starting $T_J = 25^\circ\text{C}$
- Pulse test: $PW \leq 300\mu s$, duty cycle $\leq 2\%$.
- For DESIGN AID ONLY, not subject to production testing.
- Switching time is essentially independent of operating temperature.


ORDERING INFORMATION

PART NO.	PACKAGE	PACKING
TSM80N400CF C0G	ITO-220S	50pcs / Tube


CHARACTERISTICS CURVES

($T_c = 25^\circ\text{C}$ unless otherwise noted)


Output Characteristics




Transfer Characteristics




On-Resistance vs. Drain Current




Gate-Source Voltage vs. Gate Charge



On-Resistance vs. Junction Temperature




On-Resistance vs. Gate-Source Voltage




CHARACTERISTICS CURVES

($T_C = 25^\circ\text{C}$ unless otherwise noted)


Capacitance vs. Drain-Source Voltage




BV_{DSS} vs. Junction Temperature




Maximum Safe Operating Area, Junction-to-Case



Source-Drain Diode Forward Current vs. Voltage




Normalized Thermal Transient Impedance, Junction-to-Case




PACKAGE OUTLINE DIMENSIONS (Unit: Millimeters)

ITO-220S



MARKING DIAGRAM



- G** = Halogen Free
- Y** = Year Code
- WW** = Week Code (01~52)
- F** = Factory Code

#1

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.