



Product Data Sheet

145X583

Replace "x" with 1, 2, or 3 for number of poles

Power Terminal Block

360 Amps 600 Volts AC/DC

Wire Range

- Line: (1) 3/8 - 16 X 1 7/16 stud
- Load: (2) 1/4 - 20 X 1 7/16 stud

Electrical Ratings

- 360 Amps
- 600V per UL 1059 & CSA 22.2 No.158, class B & C requirements
- SCCR of 10,000 A (default for terminal blocks).
- Factory & Field Wiring

Agency Compliance

- UR - UL Recognized Terminal Block, Evaluated to UL 1059, File No.XCFR2.E62806
- CSA - certified to C22.2 No. 158, File No. LR19766


Material Information

- Insulator base:
 - Phenolic
 - Flammability rating of insulator base UL94V0
 - Insulator base temperature rating: -40°C to 150°C (UL RTI)
- Bus bar: copper, tin plated
- Threaded stud: brass, tin plated
- Hex nut: brass, nickel plated
- Connector mounting screws: steel, zinc plated
- RoHS compliant


A Regal Brand

REGAL

Termination Specifications

Line Side	Termination Type	Torque	Stud Length	Maximum Lug/Bar Width
	Listed lugs on 3/8 - 16 stud	21.7 N·m (192 lbf·in)	1 7/16" (37mm)	2.25" (57mm)

- For use with conductors prepared with listed connectors such as single hole compression/crimp lugs or listed ring, fork or spade terminals.
- Conductor size, ampacity, temperature rating and type are dictated by the ratings of the listed lugs utilized and applicable code requirements.

Load Side	Termination Type	Torque	Stud Length	Maximum Lug/Bar Width
	Listed lugs on 1/4 - 20 stud	6.9 N·m (61 lbf·in)	1 7/16" (37mm)	2.25" (57mm)

- For use with conductors prepared with listed connectors such as single hole compression/crimp lugs or listed ring, fork or spade terminals.
- Conductor size, ampacity, temperature rating and type are dictated by the ratings of the listed lugs utilized and applicable code requirements.

Installation & Accessories

- Mounting (Panel):
 - For use with 1/4 fastener.
 - Mounting torque to be determined in end use application not to exceed 40 lbf-in (4.5 N·m).
- Covers:
 - Flat covers available upon request
 - Catalog Number: CC 145x (replace "x" with number of poles)
 - Covers are clear polycarbonate
 - Accessory covers are not intended to provide insulation for electrical spacings.
- Marker Strip: white vinyl strip with mounting screws available.
- Printing options available, consult customer service for specifications.

Drawing

