Part Number : 1719820142
Product Description : Nano-Pitch I/O Connector, Right-Angle, Surface Mount, without Cap, 42 Circuits
Series Number : 171982
Status : Not Recommended For New Design
Product Category : High-Speed I/O Connectors



Documents and Resources

Drawings

1719820142_sd.pdf

PK-171982-9000-001.pdf

PK-173307-0001-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

SYM-171982-0142-001.zip

EE-171982-0010-001.pdf

SP-171982-0010-001.zip

Specifications

AS-173162-0001-001.pdf

AS-173162-0002-001.pdf

PS-173162-0001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-

Downloaded from Arrow.com.

	DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
Category	High-Speed I/O Connectors
Series	171982
Description	Nano-Pitch I/O Connector, Right-Angle, Surface Mount, without Cap, 42 Circuits
Application	Wire-to-Board
Component Type	Receptacle
Product Name	Nano-Pitch I/O
Type	Internal
UPC	889056188364

Agency

UL	E29179

Electrical

Downloaded from Arrow.com.

Current - Maximum per Contact	0.5A
Data Rate	16.0 Gbps
Grounding to Panel	None
Shielded	No
Voltage - Maximum	30V AC (RMS)/DC

Physical

Circuits (Loaded)	42
Circuits (maximum)	42
Color - Resin	Black
Durability (mating cycles max)	50
Gender	Receptacle
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	1.070/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
Panel Mount	No
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-40° to +80°C
Termination Interface Style	Surface Mount

Downloaded from Arrow.com.

Solder Process Data

Lead-Free Process Capability	N/A

This document was generated on May 21, 2026

Downloaded from Arrow.com.