



HIRSCHMANN

A BELDEN BRAND

Product information SPIDER 1TX/1FX-MM PD EEC

Industrial Ethernet:Unmanaged Industrial Ethernet Switches:SPIDER PoE-Switches:SPIDER 1TX/1FX-MM PD EEC

<https://catalog.beldensolutions.com:443/link/57078-24455-49855-211393-206648/en/conf/uistate>

Name	SPIDER 1TX/1FX-MM PD EEC
	2 Port Switch with 1 x TX PoE PD Port and 1 x FX multimode SC port; enhanced environmental conditions
Delivery informations	
Availability	available until: 01.10.2019
Product description	
Description	2 Port Switch with 1 x TX PoE PD Port and 1 x FX multimode SC port; enhanced environmental conditions
Port type and quantity	1 x 10/100BASE-TX, 1 x PoE according to IEEE802.3af, 1 x FX multimode SC port, TP-cable, RJ45 sockets, auto-crossing, auto-negotiation, auto-polarity
Type	SPIDER 1TX/1FX-MM PD EEC
Order No.	942 051-002
Classification	
Belden brand	Hirschmann
More Interfaces	
Power supply/signaling contact	PoE feeding, no signaling contact
Network size - length of cable	
Twisted pair (TP)	0 m ... 100 m
Multimode fiber (MM) 50/125 µm	0 - 2 km
Multimode fiber (MM) 62.5/125 µm	0 - 2 km
Single mode fiber (SM) 9/125 µm	n/a
Single mode fiber (LH) 9/125 µm (long haul transceiver)	n/a
Network size - cascability	
Line - / star topology	any
Power requirements	
Operating voltage	48 VDC (36 ... 57 VDC, phantom power)
Current consumption at 48 V DC	66 mA
Power output in Btu (IT) h	10.7
Service	
Diagnostics	LEDs (power, link status, data, data rate)
Ambient conditions	
Operating temperature	-40 °C ... 70 °C
Storage/transport temperature	-40 °C ... 85 °C
Relative humidity (non-condensing)	5 % ... 95 %
MTBF	55.3 years (MIL-HDBK-217F)
Mechanical construction	
Dimensions (W x H x D)	25 mm x 100 mm x 70 mm
Mounting	DIN Rail
Weight	171 g
Protection class	IP30
EMC interference immunity	
EN 61000-4-2 electrostatic discharge (ESD)	6 kV contact discharge, 8 kV air discharge
EN 61000-4-3 electromagnetic field	10 V/m (80-1000 MHz)
EN 61000-4-4 fast transients (burst)	2 kV power line, 4 kV data line
EN 61000-4-5 surge voltage	power line: 2 kV (line/earth), 1 kV (line/line), 1 kV data line
EN 61000-4-6 conducted immunity	10 V (150 kHz-80 MHz)
EMC emitted immunity	
FCC CFR47 Part 15	FCC 47 CFR Part 15 Class A
EN 55022	EN 55022 Class A
Approvals	
Safety of industrial control equipment	cUL 508
EMV regulations for assembly in vehicles	Approval according to automotive directive 2005/83/EG (E13) in preparation
Employment in vehicles	E1

Industrial Ethernet:Unmanaged Industrial Ethernet Switches:SPIDER PoE-Switches:SPIDER 1TX/1FX-MM PD EEC

<https://catalog.beldensolutions.com:443/link/57078-24455-49855-211393-206648/en/conf/ui/state>

Scope of delivery and accessories

Scope of delivery	device, manual
-------------------	----------------

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.