Innovative Service Around the Globe YAGEO

DATA SHEET

HIGH VOLTAGE AND ANTI-SULFURATED AUTOMOTIVE GRADE CHIP RESISTORS

AH series

0.5%, 1%, 5%

sizes 0603/0805/1206

RoHS compliant

IEC 62368-1 Safety Certificate issued by UL Demko:



YAGEO

Product specification – November 03, 2025 V.4



Downloaded from Arrow.com.

SCOPE

This specification describes AH0603/0805/1206 high voltage and anti-sulfurated chip resistors with lead-free terminations made by thick film process.

APPLICATIONS

- Converter
- Printer equipment
- Battery charger
- Computer
- Power supply
- Car electronics

FEATURES

- AEC-Q200 qualified
- RoHS compliant
- Reducing environmentally hazardous wastes
- High component and equipment reliability
- Non-forbidden materials used in products/production
- Halogen Free Epoxy
- Moisture sensitivity level: MSL 1
- IEC 62368-1:2014 safety certificate (G.10.2) issued by UL Demko for the following sizes and resistance ranges:
  - 0603: 100KΩ to 10MΩ
  - 0805: 100KΩ to 22MΩ
  - 1206: 100KΩ to 27MΩ

  *Please refer to UL certification

ORDERING INFORMATION - GLOBAL PART NUMBER & 12NC

Both part numbers are identified by the series, size, tolerance, packing type, temperature coefficient, taping reel and resistance value.

YAGEO BRAND ordering code

GLOBAL PART NUMBER (PREFERRED)

AH XXXX X X X XX XXXX L
(1) (2) (3) (4) (5) (6) (7)

(1) SIZE

0603/0805/1206

(2) TOLERANCE

D = ±0.5%
F = ±1%
J = ±5%

(3) PACKAGING TYPE

R = Paper/PE taping reel
K = Embossed taping reel

(4) TEMPERATURE COEFFICIENT OF RESISTANCE

– = Base on spec

(5) TAPING REEL

07 = 7 inch dia. Reel & Standard power
7W = 7 inch dia. Reel & 2 x standard power

(6) RESISTANCE VALUE

There are 2~4 digits indicated the resistor value. Letter R/K/M is decimal point, no need to mention the last zero after R/K/M, e.g.1K2, not 1K20.

Detailed resistance rules show in table of "Resistance rule of global part number".

(7) DEFAULT CODE

Letter L is system default code for ordering only (Note)

Resistance rule of global part number

Resistance code rule	Example
XXKX (10 to 97.6 KΩ)	10K = 10,000 Ω 97K6 = 97,600 Ω
XXXK (100 to 976 KΩ)	100K = 100,000Ω 976K = 976,000Ω
XMXX (1 to 9.76 MΩ)	1M = 1,000,000 Ω 9M76 = 9,760,000 Ω
XXMX (10 to 16 MΩ)	10M = 10,000,000 Ω 27M = 27,000,000 Ω

ORDERING EXAMPLE

The ordering code of a AH1206 chip resistor, value 1 MΩ with ±5% tolerance, supplied in 7-inch tape reel is: AH1206JR-071ML.

NOTE

1. All our R-Chip products meet RoHS compliant. "LFP" of the internal 2D reel label mentions "Lead Free Process"
2. On customized label, "LFP" or specific symbol printed and the optional "L" at the end of GLOBAL PART NUMBER / 12NC can be added (both are on customer request)

Downloaded from Arrow.com.

MARKING

AH0603/0805/1206




Fig. 1 Value=10 KΩ

E-24 series: 3 digits, ±5%

First two digits for significant figure and 3rd digit for number of zeros

AH0603



Fig. 2 Value=24Ω

E-24 series: 3 digits, ±0.5% & ±1%

Exception values 10/11/13/15/20/75 of E24 series

One short bar under marking letter



Fig. 3 Value=12.4 KΩ

E-96 series: 3 digits, ±0.5% & ±1%

Including values 10/11/13/15/20/75 of E24 series

First two digits for E-96 marking rule and 3rd letter for number of zeros

AH0805/1206




Fig. 4 Value=10 KΩ

Both E-24 and E-96 series: 4 digits, ±0.5% & ±1%

First three digits for significant figure and 4th digit for number of zeros

For further marking information, please refer to data sheet "Chip resistors marking".

CONSTRUCTION

The resistor is constructed on top of a high-grade ceramic body. Internal metal electrodes are added on each end to make the contacts to the thick film resistive element. The composition of the resistive element is a noble metal imbedded into a glass and covered by a second glass to prevent environment influences. The resistor is laser trimmed to the rated resistance value. The resistor is covered with a protective epoxy coat, finally the two external terminations (matte tin on Ni-barrier) are added. See fig.5

DIMENSIONS

Table 1 For outlines see fig. 5

TYPE	L (mm)	W (mm)	H (mm)	I_1 (mm)	I_2 (mm)
AH0603	1.60 ±0.10	0.80 ±0.10	0.45 ±0.10	0.25 ±0.15	0.25 ±0.15
AH0805	2.00 ±0.10	1.25 ±0.10	0.50 ±0.10	0.35 ±0.20	0.35 ±0.20
AH1206	3.10 ±0.10	1.60 ±0.10	0.55 ±0.10	0.45 ±0.20	0.45 ±0.20

OUTLINES

For dimension see Table 1




Fig. 5 Chip resistor outlines

Downloaded from Arrow.com.

ELECTRICAL CHARACTERISTICS

Table 2

TYPE	RESISTANCE RANGE	CHARACTERISTICS					
		Rated Power	Operating Temperature Range	Max. Working Voltage	Max. Overload Voltage	Dielectric Withstanding Voltage	Temperature Coefficient of Resistance
AH0603	5% (E-24) 47Ω to 10MΩ 1% (E-24/E-96) 47Ω to 10MΩ 0.5% (E-24/E-96) 47Ω to 10MΩ	1/10W	–55 °C to +155 °C	350V	500V	500V	47Ω≤R≤10MΩ ±100ppm°C 10MΩ<R≤51MΩ ±200ppm°C
AH0805	5% (E-24) 47Ω to 51MΩ 1% (E-24/E-96) 47Ω to 51MΩ 0.5% (E-24/E-96) 47Ω to 10MΩ	1/8 W 1/4 W		400 V	800 V	800 V	
AH1206	5% (E-24) 47Ω to 51MΩ 1% (E-24/E-96) 47Ω to 51MΩ 0.5% (E-24/E-96) 47Ω to 15MΩ	1/4 W		800 V	1,600 V	1,600 V	

FOOTPRINT AND SOLDERING PROFILES

For recommended footprint and soldering profiles, please refer to data sheet "Chip resistors mounting".

PACKING STYLE AND PACKAGING QUANTITY

Table 3 Packing style and packaging quantity

PACKING STYLE	REEL DIMENSION	AH 0603	AH 0805	AH 1206
Paper/PE taping reel (R)	7" (178 mm)	5,000	5,000	5,000
Embossed taping reel (K)	7" (178 mm)	---	---	---

NOTE

1. For Paper/PE/Embossed tape and reel specification/dimensions, please refer to data sheet "Chip resistors packing".

Downloaded from Arrow.com.

FUNCTIONAL DESCRIPTION

OPERATING TEMPERATURE RANGE

Range: –55 °C to +155 °C

POWER RATING

Each type rated power at 70 °C:

AH0603=1/10W

AH0805=1/8W, 1/4W

AH1206=1/4W




Fig. 6 Maximum dissipation (P_{max}) in percentage of rated power as a function of the operating ambient temperature (T_{amb})

RATED VOLTAGE

The DC or AC (rms) continuous working voltage corresponding to the rated power is determined by the following formula:

$V = \sqrt{(P \times R)}$

or max. working voltage whichever is less

Where

V = Continuous rated DC or AC (rms) working voltage (V)

P = Rated power (W)

R = Resistance value (Ω)

Maximum working voltage can be applicable to resistors only if the resistance value is equal to or higher than the critical resistance value.

Downloaded from Arrow.com.

TESTS AND REQUIREMENTS

Table 4 Test condition, procedure and requirements

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
High Temperature Exposure	AEC-Q200 Test 3 MIL-STD-202 Method 108	1,000 hours at T_A = 155 °C, unpowered	±(1.0%+0.05Ω)
Moisture Resistance	MIL-STD-202 Method 106	Each temperature / humidity cycle is defined at 8 hours, 3 cycles / 24 hours for 10d. with 25 °C / 65 °C 95% R.H, without steps 7a & 7b, unpowered	±(2.0%+0.05Ω)
Biased Humidity	AEC-Q200 Test 7 MIL-STD-202 Method 103	1,000 hours; 85 °C / 85% RH 10% of operating power Measurement at 24±4 hours after test conclusion.	±(5.0%+0.05Ω)
Operational Life	AEC-Q200 Test 8 MIL-STD-202 Method 108	1,000 hours at 125 °C, derated voltage applied for 1.5 hours on, 0.5 hour off, still-air required	±(3.0%+0.05Ω)
Resistance to Soldering Heat	AEC-Q200 Test 15 MIL-STD-202 Method 210	Condition B, no pre-heat of samples Lead-free solder, 260±5 °C, 10±1 seconds immersion time Procedure 2 for SMD: devices fluxed and cleaned with isopropanol	±(1.0%+0.05Ω) No visible damage
Thermal Shock	MIL-STD-202 Method 107	-55/+125 °C Number of cycles is 300. Devices mounted Maximum transfer time is 20 seconds. Dwell time is 15 minutes. Air – Air	±(1.0%+0.05Ω)
ESD	AEC-Q200 Test 17 AEC-Q200-002	Human Body Model, 1 $_{pos.}$ + 1 $_{neg.}$ discharges 0201: 500V 0402/0603: 1KV 0805 and above: 2KV	±(4.0%+0.05Ω)

Downloaded from Arrow.com.

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
Solderability - Wetting	AEC-Q200 Test 18 J-STD-002	Electrical Test not required Magnification 50X SMD conditions: (a) Method B, aging 4 hours at 155 °C dry heat, dipping at 235±3 °C for 5±0.5 seconds. (b) Method B, steam aging 8 hours, dipping at 215±3 °C for 5±0.5 seconds. (c) Method D, steam aging 8 hours, dipping at 260±3 °C for 30±0.5 seconds.	Well tinned (≥95% covered) No visible damage
Board Flex	AEC-Q200 Test 21 AEC-Q200-005	Chips mounted on a 100mm x 40mm glass epoxy resin PCB (FR4) Bending for 0201/0402: 5 mm 0603/0805: 3 mm 1206 and above: 2 mm Holding time: minimum 60 seconds	±(1.0%+0.05Ω)
Temperature Coefficient of Resistance (T.C.R.)	MIL-STD-202 Method 304	At +25/–55 °C and +25/+125 °C **Formula:** $T.C.R = \frac{R_2 - R_1}{R_1(t_2 - t_1)} \times 10^6$ (ppm/°C) Where t_1=+25 °C or specified room temperature t_2=–55 °C or +125 °C test temperature R_1=resistance at reference temperature in ohms R_2=resistance at test temperature in ohms	Refer to table 2
Short Time Overload	IEC60115-1 8.1	2.5 times of rated voltage or maximum overload voltage whichever is less for 5 sec at room temperature	±(2.0%+0.05Ω)
FOS	ASTM-B-809-95* * Modified	Sulfur 750 hours, 105° C, unpowered	±(4.0%+0.05Ω)

Downloaded from Arrow.com.

REVISION HISTORY

REVISION	DATE	CHANGE NOTIFICATION	DESCRIPTION
Version 4	Nov. 03, 2025	-	- Add double power for AH0805
Version 3	Sep. 22, 2025	-	- Extend resistor Range of AH0805 and AH1206
Version 2	Mar. 02, 2023	-	- TCR updated
Version 1	Aug. 02, 2022	-	- l2 dimension updated, for size1206.
Version 0	Sep. 10, 2020	-	- First issue of this specification

Downloaded from Arrow.com.

LEGAL DISCLAIMER

YAGEO, its distributors and agents (collectively, "YAGEO"), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. YAGEO may make changes, modifications and/or improvements to product related information at any time and without notice.

YAGEO makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, YAGEO disclaims (i) any and all liability arising out of the application or use of any YAGEO product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non -infringement and merchantability.

YAGEO products are designed for general purpose applications under normal operation and usage conditions. Please contact YAGEO for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property: Aerospace equipment (artificial satellite, rocket, etc.), Atomic energy-related equipment, Aviation equipment, Disaster prevention equipment, crime prevention equipment, Electric heating apparatus, burning equipment, Highly public information network equipment, data-processing equipment , Medical devices, Military equipment, Power generation control equipment, Safety equipment, Traffic signal equipment, Transportation equipment and Undersea equipment, or for any other application or use in which the failure of YAGEO products could result in personal injury or death, or serious property damage. Particularly **YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.**

Information provided here is intended to indicate product specifications only. YAGEO reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.

Downloaded from Arrow.com.