






NOTE:

- Material:
Base: Nylon 6T + 30% GF. UL 94V-0, Color Nature
Contact: Phosphor Bronze
Tab: Brass, with Matte Tin plated
PAD: Nylon 6T + 30% GF. UL 94V-0, Color Nature
- For Lead Free Reflow Process

ORDERING CODE

CI11 ** M 1 V RO -NH
① ② ③ ④ ⑤ ⑥ ⑦



- Series No.
- Contacts:
- M= SMT type header
- Plating:
1= 2.54μm(100μ") Min. Matte Tin
Plated over 1.27μm(50μ") Nickel
2= Gold flash plated over
1.27μm(50μ") Nickel
- Type: V= Straight
- Other option:
RO= Tape & reel packing
(With pick & place pad)(Standard)
RN= Tape & reel packing
(Without pack & place pad)
TO= Tube packing
(Without pack & place pad)
- NH= For Lead Free Reflow Processes and Halogen-Free



DIM. A = 1.00 x NO. OF SPACES

DIM. B = DIM. A + 3.0

* AVAILABLE IN 2 THROUGH 18,20 AND 26 CIRCUITS



Halogen-Free

Lead Free Process


RoHS Compliant

7	Iuo	1/4-26'	ECRQ125042/ECNT125362		DATE	UNIT: mm / inch	TITLE: 1.00MM(.079")	 瀚荃股份有限公司 CviLux Corporation			
6	Iuo	7/8-25'	ECRQ125020/ECNT125172	DRAWN BY: Iuo	1/4-26'	TOLERANCE UNLESS OTHERWISE SPECIFIED	WIRE TO BOARD CONNECTOR				
5	Sun	6/10-21'	ECRH121018/ECNT121139	ENGINEER: Sun	1/4-26'	.X ± 0.30/.012 .XX ± 0.20/.008 .XXX ± 0.10/.004	MATERIAL:	DRAWING NO. CI1152SH SCALE 6 / 1 PART NO. CI11**M*V**-NH SHEET 1 OF 2			
4	Sun	7/15-20'	ECRH120028/ECNT120184	CHECKED BY: Eisley	1/4-26'	.X' ± 1" .X' ± .XX' ±	FINISH:				
SYM	NAME	DATE	REVISIONS	APPROVED BY: Eisley	1/4-26'						


CviLux Corp
2026-01-07
ISSUED

NOTE :

- * Reel Material : HIPS
- * Carrier Material : Clear, Conductive Polystyrene Alloy
- * Cover Tape Material : Polyester
- * Cover Tape Peel Strength : 0.1N – 1.3N
- * Carrier camber is within 1mm in 100mm
- * All dimensions meet EIA-481-2 & EIA-481-3 requirements.
- * Quantity : 1000 PCS/Reel



Circuits	Dimension					Packing (Reel/Carton)
	E	F	W1	W2	W3	
2~6	16.0(.630)	—	16.5(.650)	22.5(.886)	16.5(.650)	11
7~13	24.0(.945)	—	24.5(.965)	30.5(1.201)	24.5(.965)	9
14~18	32.0(1.260)	28.40(1.118)	32.5(1.280)	38.5(1.516)	32.5(1.280)	7
20,26	44.0(1.732)	40.40(1.591)	44.5(1.752)	50.5(1.988)	44.5(1.752)	5



RoHS Compliant

7	luo	1/4-26'	ECRQ125042/ECNT125362		DATE	UNIT: mm / inch	TITLE: 1.00MM(.079")	瀚荃股份有限公司 CviLux Corporation			
6	luo	7/8-25'	ECRQ125020/ECNT125172	DRAWN BY:	luo	1/4-26'	WIRE TO BOARD CONNECTOR				
5	Sun	6/10-21'	ECRH121018/ECNT121139	ENGINEER:	Sun	1/4-26'	MATERIAL:	DRAWING NO.	CI1152SH	PART NO.	CI11**M*V**-NH
4	Sun	7/15-20'	ECRH120028/ECNT120184	CHECKED BY:	Eisley	1/4-26'	FINISH:	SCALE		SHEET	2 OF 2
SYM	NAME	DATE	REVISIONS	APPROVED BY:	Eisley	1/4-26'					

CviLux Corp
2026-01-07
ISSUED