

Product data sheet

Specifications



APC NetShelter Power Cord Kit (6 ea), Locking, C13 to C14, 1.8m, North America

AP8706S-NA

Overview

Presentation	Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.
Lead time	Usually in Stock

Main

Product or component type	Power cord
Input Connection Type	IEC 60320 C14
Cable length	1.8 m
Number of cables	6

Physical

Colour	Black
Height	24 cm
Width	7.5 cm
Depth	5.5 cm
Net weight	1.35 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable

Input

Max line current	10 A
Input current limits	10 A

Output

Max current draw	10 A
Number of power socket outlets	1 IEC 60320 C13
Power cable length	1.8 m

Conformance

Product certifications	CSA UL listed
------------------------	------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental

Ambient air temperature for operation	0...105 °C
Relative humidity	20...80 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...105 °C
Storage Relative Humidity	20...80 %
Storage altitude	0...15240 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	24 cm
Package 1 Width	5.5 cm
Package 1 Length	7.5 cm
Package 1 Weight	1.35 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

 Environmental footprint	
Total lifecycle Carbon footprint	425
Environmental Disclosure	Product Environmental Profile

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
Halogen-free status	Product contains halogen above thresholds

Use Again

 Repack and remanufacture	
End of life manual availability	End of Life Information
Take-back	Yes
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins