



Part Number : [1200720258](#)

Product Description : M12 Signal, C-Coded, Single-Ended Cordset, 3 Poles, Female (90°) to Pigtail, 22 AWG, Yellow Shielded PVC Cable, Yellow Overmold, 6.10m (20.0') Length

Series Number : 120072

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : 703001D02F200



Documents and Resources

Drawings

[1200720258_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Di-(2-ethylhexyl)phthalat per ED/21/2016 (20 June 2016)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120072
Description	M12 Signal, C-Coded, Single-Ended Cordset, 3 Poles, Female (90°) to Pigtail, 22 AWG, Yellow Shielded PVC Cable, Yellow Overmold, 6.10m (20.0') Length
IP Rating	IP67
Product Name	M12 Signal, Micro-Change (M12)
Type	Single Ended
UPC	78678875914

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Cable Diameter	5.72mm (.225")
Cable Length	6.10m (20.0')
Color - Cable Jacket	Yellow
Connector End A	M12 Signal

Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	C-Coded
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	TPC
Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - O-Ring	Nitrile Rubber
Material - Plating Mating	Gold
Net Weight	321.560/g
Orientation	90° to Pigtail
Poles	3
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	UL 2661
Wire Size (AWG)	22

This document was generated on Apr 23, 2026