

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0482040001

Status:


Active

Overview:

Consumer USB Products

Description:

Universal Serial Bus (USB) Shielded I/O Receptacle, Type A Upright Right Angle, Reverse Mount, Solder Tail Length 2.90mm, 3.70mm Beveled Metal Pins, PCB Thickness 1.60mm, 0.76µm Gold (Au) Plating, Lead-Free



Series image - Reference only

Documents:

3D Model

Drawing (PDF)

Product Specification PS-48204-001-001 (PDF)

Product Specification TS-48204-001-001 (PDF)

Packaging Specification PK-48204-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	I/O Connectors
Series	48204
Application	Wire-to-Board
Comments	Reverse Mount Type Beveled Metal Pin Length: 3.70mm
Component Type	Receptacle
Overview	Consumer USB Products
Product Name	USB 2.0
Type	A
UPC	822348794614
Physical	
Boot Color	N/A
Circuits (Loaded)	4
Circuits (maximum)	4
Gender	Receptacle
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	2.678/g
Number of Rows	4
Orientation	Upright
PC Tail Length	2.90mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	N/A
Plating min - Mating	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55°C to +85°C
Termination Interface: Style	Through Hole
Waterproof / Dustproof	No
Electrical	
Current - Maximum per Contact	1.5A
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V AC (RMS)/DC

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per

-ED/01/2017 (12

January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

48204 Series

Mates With

USB Type A Plug

Solder Process Data

Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	265

Material Info

Reference - Drawing Numbers

Electrical Model Document	EE-48204-001
Packaging Specification	PK-48204-001
Product Specification	PS-48204-001-001, TS-48204-001-001
Sales Drawing	SD-48204-001

This document was generated on 03/07/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION