2384003-1 ✔ ACTIVE

DEUTSCH | DEUTSCH DT Highspeed

TE Internal #: 2384003-1

Cavity Plug, -40 – 125 °C [-40 – 257 °F], Black, DEUTSCH DT Highspeed

View on TE.com >

Connectors > Connector Accessories > Connector Seals & Cavity Plugs > DT Highspeed Connectors seals and plugs







Connector Seal & Plug Type: **Cavity Plug**

Operating Temperature Range: **-40 – 125 °C [-40 – 257 °F]**

Primary Product Color: **Black**

Operating Temperature (Max): **125 °C [257 °F]**

All DT Highspeed Connectors seals and plugs (3)

Features

Product Type Features

Connector Seal & Plug Type	Cavity Plug

Body Features

Primary Product Color	Black

Usage Conditions

Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]
Operating Temperature (Max)	125 °C[257 °F]

Packaging Features

Packaging Method	Tray

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant

Downloaded from Arrow.com.

China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




TE Part # 9-2367359-2
2POS,PIN CSS SIZE 20,HDR ASSY, 180DEG



TE Part # CAT-AI5-DHPHAR
DT Highspeed Connector headers



TE Part # CAT-AI5-DHCH
DT Highspeed Connectors housings




TE Part # 9-2367359-3
2POS,PIN CSS SIZE 20,HDR ASSY, 180DEG



TE Part # 9-2383999-1
4POS,DIA 1MM,PIN HSG ASSY,SLD

Also in the Series | DEUTSCH DT Highspeed

Downloaded from Arrow.com.




Automotive Connector EMC Shielding (6)



Automotive Housings(3)



Infotainment & Multimedia Cable Assemblies(15)



Other Automotive Connector Accessories(7)

Customers Also Bought



TE Part #2325098-6
MNTG CLIP,ENETSEAL PLUS



TE Part #CAT-AI5-EH
enetSEAL+ Ethernet Connector Housings




TE Part #2338212-2
PLUG SOCKET ASSY, 4P, W2W, SEALED COAX



TE Part #2367337-1
DT Highspeed, Socket Housing Assembly



TE Part #2367337-3
DT Highspeed, Socket Housing Assembly



TE Part #2-2374559-1
1P AS16 CX, BLIND CAP KEY A,CONN KIT



TE Part #2375997-2
DT04-08PB-P093,REC,8P BLK,BUSBAR G,4X2,B



TE Part #2458925-1
SDE DT Highspeed Ferrule 0.35 mm Tool

Documents

Product Drawings

BLIND CONNECTOR,REC HSG ASSY,DATA DT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2384003-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2384003-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2384003-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Downloaded from Arrow.com.

Product Specifications

Application Specification

English

Downloaded from Arrow.com.