


TAPE ON REEL PACKAGING ACCORDING TO DIN IEC 60286-3
PACKAGING UNIT: 75 PCS






INSPECTION LEVEL 2 AND 3: CONTROL CHART REQUIRED
(72) PROOF OF MEAN VALUE, STANDARD DEVIATION AND MACHINE CAPABILITY


⑦ PROOF OF VALUES OR PROOF OF ATTRIBUTIVE TEST




CONSIDER MOUNTING POSITION; PEG RIGHT



PCB-LAYOUT PROPOSAL



PART PACKED WITH HOOD



SCALE 2:1
3D VIEW

1	-	TAPE AND REEL	6
1	-	HOOD	5
1	-	SOLDER CLIP LEFT	4
1	-	SOLDER CLIP RIGHT	3
5	-	PINS	2
1	-	HOUSING	1
474331-E	REV	DESCRIPTION	ITEM NO.
-	REV OF EACH ASSY NO. (WHEN BLANK, USE DWG. REV)		
QTY	PARTS LIST		

V=TURNED CONTACT (PCB SIDE CAN BE USED WITH POTTED COMPOUND)
 *=VERSION: WITH HOOD, WITH CUT-IN, Ø8.2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N K NIKHIL 25JUL2023 CHK M SZELAG 27JUL2023 APVD J DE BRUIN 27JUL2023		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 2768-mK ISO 8015		NAME M12 MALE, UNI CODE, 5P, 10.5MM SMT, DI V * -	
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 108-94887 APPLICATION SPEC 114-94781			
MATERIAL - FINISH -		WEIGHT -		SIZE A2 CAGE CODE 00779 DRAWING NO C=474331-E RESTRICTED TO -	
		CUSTOMER DRAWING		SCALE 5:1	SHEET 1 of 1
				REV E2	

1. DRAWING SPECIFICATION ACCORDING TO DOCUMENT
5_3_16-DOC-1806-00915

2. COPLANARITY OF ALL CONTACTS AND CLIPS $\leq 0.1\text{MM}$