

Quick Links

Cross reference

RoHS/LF P/N Search

Industry Standards

Alphabetical List

Documentation

3D model search


Customer drawing search

Multi Selection Search

Search by category

Start > Search=HM2P07PDJ1N1N9LF* > HM2P07PDJ1N1N9LF

HM2P07PDJ1N1N9LF
HM2P07PDJ1N1N9LF - Millipacs® : 2 mm Hard Metric
Millipacs Series 5 row vertical Header, Module Type A with
110 signal pins , shielded and RoHS compatable



Customer drawing



Product Environmental Compliance Report

ACTIVE

RoHS
Compliant



Distributor Stock

**PRIORITY
PART**

[Print Datasheet](#)

FCI Brings You More

[Contact our sales/technical support](#)
 [Sample request](#)

Specifications

Download document

Mating Half

General Dimensional Electrical Mechanical Physical Approvals / Certifications Mounting Other Features

General	
Gender	Header
Number of contacts	110
Number of rows	5
Orientation	Vertical
Product Type	Header
Series	Module Type A
Shielded	Yes
Number of levels (Contact)	Refer to Customer Drawing
Dimensional	
Length (Tail)	Short Tail (3.7 mm)
Electrical	
Current rating	1.5A at 20°C, 1A at 70°C
Resistance (Contact)	20 milli ohms max.
Resistance (Insulation)	10,000 M-ohms min.
Voltage rating	750V rms
Mechanical	
Withdrawal Force	0.15N min. per Contact Pair
Hertz stress	200 Kpsi min.
Mating force (Signal)	0.75N max. per Contact Pair
Physical	
Material (Contact)	Copper alloy
Material (Housing)	Thermoplastic (UL94 V-0)
Temperature (Operating - range)	-55°C to +125°C
Approvals / Certifications	
Approvals / Certifications	UL Approved
UL File Number	E66906
Mounting	
Mounting style (Board)	Press-Fit
Other Features	
Packaging (Type)	Tray

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.