




Part Number : [903273316](#)
Product Description : Picoflex PF-50, Low Profile,
IDT Receptacle, 16 Circuits, White, Gold (Au) Plated,
Bag
Series Number : 90327
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

[903273316 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[908140000-AS-000.pdf](#)

[PK-90327-001-001.pdf](#)

[PS-99020-0011-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 47; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	90327
Description	Picoflex PF-50, Low Profile, IDT Receptacle, 16 Circuits, White, Gold (Au) Plated, Bag
Comments	Low Profile
Component Type	Housing
Product Name	Picoflex
UPC	800753669840

Agency

CSA	LR19980
UL	E29179

Electrical

Voltage - Maximum	250V
-------------------	------

Physical

Circuits (Loaded)	16
-------------------	----

Circuits (maximum)	16
Color - Resin	White
Durability (mating cycles max)	100
Entry Angle	Vertical
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Polyester
Net Weight	2.425/g
Number of Rows	2
Packaging Type	Bag
PCB Locator	No
PCB Retention	No
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Shrouded
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	IDT or Pierce
Wire/Cable Type	Ribbon Cable
Wire Insulation Diameter	1.00mm max.
Wire Size (AWG)	26, 28

Mates With / Use With

Mates with Part(s)

Description	Part Number
Picoflex PF-50 Vertical Low Profile Headers	<u>90325</u>

Picoflex PF-50 Vertical Low Profile Headers	<u>90779</u>
Picoflex PF-50 Vertical Surface Mount Headers	<u>90814</u>

Application Tooling

Global

Description	Part Number
Extractor Tool for Connectors	<u>621006000</u>
Extraction Tool for Picoflex PF-50 Connectors, 4-26 Circuits	<u>690081070</u>
PremiumGrade Hand Crimp Tool for Picoflex PF-50 IDT Receptacle, 4-26 Circuits, 28-26 AWG Flat Cable, 1.00mm max. Thickness	<u>690081090</u>
Arbor Press Fixture	<u>690201902</u>
Semi-Automatic Bench Press PB14 for 4-26 Circuit	<u>691271001</u>
Semi-Automatic PB14 Bench Press with Auto De-reeling	<u>691271004</u>
Assembly of De-Tape Unit for Semi-Automatic Bench Press PB14	<u>691275045</u>

This document was generated on May 25, 2026