

Terminal Part Number: 12191055
Surface Plating: AU
Material Thickness [mm]: 0,25
Cross Section [mm²]: 0,35 | 0,50

This document is non-contractual
and for information only.

For more information, please
consult your local sales office



Cable Type codes: 1005
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 1,45 - 1,88
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1005 0,35		1,60	55	0,85	0,05	1,85	0,10	1,80	0,10	2,50	0,10
1005 0,50		1,74	80	0,90	0,05	1,85	0,10	1,80	0,10	2,40	0,10

Cable type code legend:

1005:

Industry Designator: SAE
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: PVC, PVDF, XLPE
Insul. Wall Designator: THIN



Terminal Part Number: 12191055

Surface Plating: AU

Material Thickness [mm]: 0,25

Cross Section [mm²]: 0,35

*This document is non-contractual
and for information only.*

*For more information, please
consult your local sales office*

Cable Type codes: 1047

Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY

Insulation Range Φ[mm]: 1,40 - 1,75

Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1047 0,35		1,58	70	0,85	0,05	1,85	0,10	1,80	0,10	2,50	0,10

Cable type code legend:

1047:

Industry Designator: SAE

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: PVC, XLPE

Insul. Wall Designator: THIN

