

51494-2 ✓ ACTIVE




SHV

TE Internal #: 51494-2

SHV Connector, Jack, Threaded, .3 GHz, Cable-to-Board, 1 Position, Wire & Cable, Panel Mount, -65 – 200 °C [-85 – 392 °F], Solder, Straight, SHV

[View on TE.com >](#)

Connectors > RF Connectors > Coax Connectors



RF Interface: **SHV**

RF Connector Style: **Jack**

RF Connector Mated Outer Diameter (Approximate): **12.7 mm [.5 in]**

RF Connector Coupling Mechanism: **Threaded**

Operating Frequency Range: **.3 GHz**

Features

Product Type Features

RF Interface	SHV
RF Connector Style	Jack
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	1
Number of Coaxial Contacts	1

Body Features

Body Material	Brass
Body Plating Material	Nickel

Contact Features

RF Connector Center Contact Underplating Material	Nickel
RF Connector Center Contact Plating Thickness	1.27 µm[50 µin]



RF Connector Center Contact Plating Material	Gold (Au)
--	-----------

RF Connector Center Contact Material	Brass
--------------------------------------	-------

Termination Features

Termination Method to Wire & Cable	Solder
------------------------------------	--------

Mechanical Attachment

RF Connector Coupling Mechanism	Threaded
---------------------------------	----------

Connector Mounting Type	Panel Mount
-------------------------	-------------

RF Contact Captivation Method	Mechanical
-------------------------------	------------

Detent	Without
--------	---------

Housing Features

Body Orientation	Straight
------------------	----------

Dimensions

Panel Thickness (Recommended)	4.75 mm[.187 in]
-------------------------------	------------------

RF Connector Mated Outer Diameter (Approximate)	12.7 mm[.5 in]
---	----------------

Usage Conditions

Operating Temperature Range	-65 – 200 °C[-85 – 392 °F]
-----------------------------	----------------------------

Operation/Application

Operating Frequency Range	.3 GHz
---------------------------	--------

Packaging Features

Packaging Method	Carton
------------------	--------

Other

Dielectric Material	Polytetrafluoroethylene (PTFE)
---------------------	--------------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
------------------------------	---------------------------

EU ELV Directive 2000/53/EC	Compliant with Exemptions
-----------------------------	---------------------------

China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
---	--

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250)
--	--



SVHC > Threshold:

Pb (3.7% in Component)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5051426-8
SHV Plug Str Crimp RG-174, RG-188



TE Part # 5225059-3
SHV Jack Str Bulkhead Crimp RG-59, RG-62



TE Part # 5051426-5
SAFE HIGH VOLTAGE PLUG



TE Part # 5051426-4
SAFE HIGH VOLTAGE PLUG



TE Part # 5225087-5
SHV JACK



TE Part # 51426-2
SAFE HIGH VOLTAGE PLUG



TE Part # 5051426-2
SAFE HIGH VOLTAGE PLUG

Also in the Series

Customers Also Bought




TE Part #20024308-00
K10-HS20L6B-100k0-G20 FSW




TE Part #810106-SF
FN2030-20-08



TE Part #812253-SF
FN9289B-6-06




TE Part #1623746-4
ER74 120R 5% AMMO PK




TE Part #CAT-C339-H85913
Power Resistors: Aluminum Housed,
HSA




TE Part #3-6609106-4
PS00XDHX0=C1187



TE Part #G-W0400
KAPPE,TO-8,H317,6MM(SL16300001



TE Part #G-VPSCO-005
VPS025A



TE Part #C5001PC26A1
THERMISTOR ASSEMBLY

Documents

Product Drawings

[STD HIGH VOLTAGE BLKHD RECEPT](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_51494-2_H.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_51494-2_H.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_51494-2_H.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

51494-2

SHV Connector, Jack, Threaded, .3 GHz, Cable-to-Board, 1 Position, Wire & Cable,
Panel Mount, -65 – 200 °C [-85 – 392 °F], Solder, Straight, SHV



Product Specification

English

Product Specification

English