Pushing Performance
Since 1945

# Han 6ES Press - F




Image is for illustration purposes only. Please refer to product description.

| | |
|---|---|
| Part number | 09 33 006 2748 |
| Specification | Han 6ES Press - F |
| HARTING eCatalogue | https://harting.com/09330062748 |

## Identification

| | |
|---|---|
| Category | Inserts |
| Series | Han® ES Press |

## Version

| | |
|---|---|
| Termination method | Cage-clamp termination |
| Gender | Female |
| Size | 6 B |
| Number of contacts | 6 |
| PE contact | Yes |
| Details | Blue slide<br>for hoods/housings high construction only |

## Technical characteristics

| | |
|---|---|
| Conductor cross-section (mm²) | 0.14 ... 2.5 mm² |
| Conductor cross-section (AWG) | AWG 26 ... AWG 14 |
| Rated current | 16 A |
| Rated voltage | 500 V |
| Rated impulse voltage | 6 kV |
| Pollution degree | 3 |
| Rated voltage acc. to UL | 600 V |
| Rated voltage acc. to CSA | 600 V |
| Insulation resistance | $>10^{10}$ Ω |
| Contact resistance | ≤3 mΩ |


HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

## Technical characteristics

| | |
|---|---|
| Stripping length | 9 ... 11 mm |
| Tightening torque | 1.2 Nm PE screw M4 |
| Recommended screw driver | Slotted 0.8 x 4.5<br>PH2 |
| Limiting temperature | -40 ... +125 °C |
| Mating cycles | ≥500 |

## Material properties

| | |
|---|---|
| Material (insert) | Polycarbonate (PC) |
| Colour (insert) | RAL 7032 (pebble grey) |
| Material (contacts) | Copper alloy |
| Surface (contacts) | Silver plated |
| Colour (accessories) | Blue |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant with exemption |
| RoHS exemptions | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate<br>Lead |
| ECHA SCIP number | 5dbb3851-b94e-4e88-97a1-571845975242 |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead<br>Nickel |
| Fire protection on railway vehicles | EN 45545-2 (2020-08) + A1 (2023-10) |
| Requirement set with Hazard Levels | R22 (HL 1-3)<br>R23 (HL 1-3) |

## Specifications and approvals

| | |
|---|---|
| Specifications | IEC 60664-1<br>IEC 61984 |
| UL / CSA | UL 1977 ECBT2.E235076<br>CSA-C22.2 No. 182.3 PVVA8.E318390 |


HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

## Specifications and approvals

| | |
|---|---|
| Approvals | DNV GL |

## Commercial data

| | |
|---|---|
| Packaging size | 1 |
| Net weight | 56.07 g |
| Country of origin | Germany |
| European customs tariff number | 85366990 |
| GTIN | 5713140161863 |
| eCl@ss | 27440205 Contact insert for industrial connectors |
| ETIM | EC000438 |
| UNSPSC 24.0 | 39121522 |


HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.