



NC5FBV

PHASE OUT 5 pole female XLR receptacle,
grounding: separate ground contact to mating
connector shell and front panel, vertical PCB mount

Same as A series with exception of a metal
mounting flange featuring continuous
circumferential ground contact to chassis for best
EMC practice.

Features & Benefits

- ✓ Smallest XLR receptacles, highest packing density
- ✓ Metal mounting flange featuring continuous circumferential ground contact to chassis for best EMC and RF protection
- ✓ Fork type female contact
- ✓ Housing flammability UL 94 V-0

Technical Information

Product	
Title	NC5FBV
Connection Type	XLR
Gender	female

Electrical	
Capacitance between contacts	$\leq 7 \text{ pF}$
Contact resistance	$\leq 6 \text{ m}\Omega$
Dielectric strength	1,5 kVdc
Insulation resistance	$> 10 \text{ G}\Omega$ (initial)
Rated current per contact	3 A
Rated voltage	$< 50 \text{ V}$
Grounding Options	Separate ground contact connected to mating connector shell and front panel, no connection to Pin 1

Mechanical	
Insertion force	$\leq 20 \text{ N}$
Withdrawal force	$\leq 20 \text{ N}$
Lifetime	> 1000 mating cycles
Wiresize	
Wiring	vertical PCB mount
Locking device	Latch lock
Mounting direction	Rear mounting
Chassis shape	B
Mounting	A-Screw

Material	
Contacts	Bronze (CuSn6)
Insert	PA66
Locking element	Steel Ck67
Locking element plating	Nickel
Ring	Zinc diecast (ZnAl4Cu1)
Flange	Metal

Environmental	
Flammability	UL 94 V-0
Standard compliance	IEC 61076-2-103
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C