





REV.	DATE	DESCRIPTION
NC	06/23/98	INITIAL RELEASE
A	02/24/03	UPDATE DRAWING FORMAT



CRIMP NOTES:

1. CRIMPED FERRULE
HEX CRIMP SIZE .429"
2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .100"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex												
8						DRAWN	G.R.S.							07/20/05	PART DESCRIPTION BNC CRIMP PLUG (FOR RG-214 CABLE)					
7						CHECKED														
6							ISSUED		PART NO. 112589											
5						SHEET	1 OF 1													
4	FERRULE	BRASS	NICKEL	1			CAD FILE	C:/112/112589.DWG	DWG. NO.	112589.DWG	REV.	A	SIZE	A	SCALE	NA				
3	CONTACT PIN	BRASS	GOLD	1																
2	INSULATOR	TEFLON	NATURAL	1																
1	SHELL/BODY	BRASS	NICKEL	1																
	DESCRIPTION	MATERIAL	FINISH	QTY																