



Color: ■ gray

Technical data	
Suitable	for end stops (249-116 and 249-117); for 1 marker or self-adhesive label and transparent protective marker cover
Properties	Snap-on type and adjustable in height from 43.5 mm to 59.5 mm
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0

Physical data	
Width	10 mm / 0.394 inches

Material data	
Color	gray
Weight	1.5 g
Fire load	0.046 MJ

Commercial data	
Product Group	2 (Terminal Block Accessories)
PU (SPU)	50 (25) pcs
Packaging type	Box
Country of origin	DE
GTIN	4017332188371
Customs tariff number	39269097900

Product Classification	
UNSPSC	39121702
eCl@ss 10.0	27-14-40-75
eCl@ss 9.0	27-14-40-75
ETIM 9.0	EC002248
ETIM 8.0	EC002248
ECCN	NO US CLASSIFICATION



Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Downloads	
Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 249-119	

Documentation				
Bid Text				
249-119	19.02.2019	xml	2.79 KB	
249-119	04.01.2018	doc	24.00 KB	

CAD/CAE-Data	
CAD data	CAE data
2D/3D Models 249-119	EPLAN Data Portal 249-119
	WSCAD Universe 249-119
	ZUKEN Portal 249-119

1 Compatible Products			
1.1 Optional Accessories			
1.1.1 Marking			
1.1.1.1 Label			
 Item No.: 210-345 Labels; for laser printer; permanent adhesive; 9.5 x 25 mm; white	 Item No.: 210-808 Labels; for Smart Printer; 9.5 x 25 mm; white	 Item No.: 210-807 Labels; for Smart Printer; permanent adhesive; 8 x 20 mm; 3000 pieces on roll; white	 Item No.: 210-708 Labels; for TP printers; 9.5 x 25 mm; white

1.1.1.2 Marker	
 Item No.: 209-113 Cardboard signs; for laser printer; 9.5 x 25 mm; white	

1.1.1.3 Protective marker cover




Item No.: 209-114

Protection cover; transparent

Installation Notes

Application



This system can be used as an additional group marker carrier or continuous marking strip carrier for terminal strips or single-deck rail-mount terminal blocks, e.g., for:

- DIN-35 rail-mount terminal strips (264 Series)
- Single-deck rail-mount terminal blocks (279 to 284 Series) with a maximum height of 49 mm (1.93 inch) from upper edge of DIN-rail (observe conductor radius)Receptacles for:
 - 1 x marker
 - 2 x WMB Multi marker or
 - 3 x WCB Combi marker or
 - 1 x WFB continuous marking strip