

STRADA-IP-2X6-VSM

IESNA Type V (square) beam for wide area lighting such as car parks

SPECIFICATION:

Dimensions	173.0 x 71.4
Height	8 mm
Fastening	screw
Ingress protection classes	IP67
ROHS compliant	yes ⓘ




MATERIALS:

Component	Type	Material	Colour	Finish	Length (mm)
STRADA-IP-2X6-VSM	Multi-lens	PMMA	clear		
2X6-SEAL25	Seal	Silicone	white		

ORDERING INFORMATION:

Component		Qty in box	MOQ	MPQ	Box weight (kg)
CS15020_STRADA-IP-2X6-VSM	Multi-lens	120	40	40	6.6
» Box size: 476 x 273 x 247 mm					




See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (MEASURED):




LED Bridgelux SMD 5050
 FWHM / FWTM 136.0° / 146.0°
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED QUICK FLUX 2x6 LED XG xxx G7+
 FWHM / FWTM Asymmetric
 Efficiency 94 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED QUICK FLUX 2x6 LED XT xxx G5
 FWHM / FWTM 136.0° / 149.0°
 Efficiency 94 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):




LED XP-G2
 FWHM / FWTM 140.0° / 146.0°
 Efficiency %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED XP-L HD
 FWHM / FWTM 145.0° / 154.0°
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED XP-L2
 FWHM / FWTM 142.0° / 159.0°
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):




LED XT-E
 FWHM / FWTM 142.0° / 158.0°
 Efficiency 94 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED XT-E HE
 FWHM / FWTM 132.0° / 145.0°
 Efficiency 94 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED PrevaLED Brick HP IP 2x6
 FWHM / FWTM 138.0° / 146.0°
 Efficiency 97 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):




LED LUXEON T
FWHM / FWTM 137.0° / 142.0°
Efficiency 94 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files




LED LUXEON V
FWHM / FWTM 139.0° / 149.0°
Efficiency 94 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files



LED LUXEON V2
FWHM / FWTM 136.0° / 144.0°
Efficiency 94 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):




LED LUXEON XR-TX (L2T0-xxxx012M0000)
 FWHM / FWTM 137.0° / 145.0°
 Efficiency 94 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED SST-10-B130
 FWHM / FWTM 138.0° / 146.0°
 Efficiency 96 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type Deep Red
 Required components:



Light distribution files



LED RecLED 146x45mm 2900lm 730 2x6 IP G1
 FWHM / FWTM Asymmetric
 Efficiency 97 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):




LED NVSW219D
 FWHM / FWTM 141.0° / 150.0°
 Efficiency 94 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED NVSW219F
 FWHM / FWTM 141.0° / 147.0°
 Efficiency 94 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED NVSW319B
 FWHM / FWTM 145.0° / 153.0°
 Efficiency 94 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):




LED NVSW3x9A
 FWHM / FWTM 140.0° / 149.0°
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED NVSxx19B/NVSxx19C
 FWHM / FWTM 140.0° / 149.0°
 Efficiency 94 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED Duris S8
 FWHM / FWTM 137.0° / 148.0°
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):

PHILIPS


LED Fortimo FastFlex LED 2x6 DP G4
 FWHM / FWTM 140.0° / 146.0°
 Efficiency 94 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

PHILIPS


LED Fortimo FastFlex LED 2x6 DP G5
 FWHM / FWTM 139.0° / 148.0°
 Efficiency 97 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

PHILIPS

LED Fortimo FastFlex LED 2x6 DP HE
 FWHM / FWTM 138.0° / 150.0°
 Efficiency 98 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):

SAMSUNG


LED	HiLOM RM12 ZP (LH502C)
FWHM / FWTM	138.0° / 150.0°
Efficiency	98 %
Peak intensity	0.4 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	



Light distribution files

SCIOLUX


LED	BALAM-VP-5250-750-36
FWHM / FWTM	134.0° / 147.0°
Efficiency	97 %
Peak intensity	0.4 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	



Light distribution files

SCIOLUX

LED	ROY-S26XPL2 (XP-L2)
FWHM / FWTM	141.0° / 158.0°
Efficiency	94 %
Peak intensity	0.4 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	




Light distribution files

OPTICAL RESULTS (MEASURED):




LED XLE-S22C4XTEHE (XT-E HE)
 FWHM / FWTM 132.0° / 145.0°
 Efficiency 94 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED XLE-S26XHP35 (XHP35 HD)
 FWHM / FWTM 148.0° / 160.0°
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED 2x6 5050 module - SMJD-3625012F-XX
 FWHM / FWTM 135.0° / 146.0°
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):




LED SMJQ-D36W12Mx
 FWHM / FWTM 131.0° / 141.0°
 Efficiency 94 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED SMJQ-D36W12Px
 FWHM / FWTM 137.0° / 146.0°
 Efficiency 94 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED Z5M3
 FWHM / FWTM 141.0° / 154.0°
 Efficiency 97 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):




LED Z8Y22
FWHM / FWTM 131.0° / 141.0°
Efficiency 94 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files




LED Z8Y22P
FWHM / FWTM 137.0° / 146.0°
Efficiency 94 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

TRIDONIC

LED RLE 2x6 3000lm HP EXC2 OTD
FWHM / FWTM 138.0° / 144.0°
Efficiency 94 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):

TRIDONIC

LED RLE 2x6 4500lm HP HE EXC3 OTD Z19
 FWHM / FWTM 137.0° / 150.0°
 Efficiency 98 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED J Series 5050 Round LES
 FWHM / FWTM 143.0° / 156.0°
 Efficiency 94 %
 Peak intensity 0.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED J Series 5050 Round LES
 FWHM / FWTM 141.0° / 153.0°
 Efficiency 95 %
 Peak intensity 0.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED J Series 5050B 30V K Class
 FWHM / FWTM 143.0° / 159.0°
 Efficiency 90 %
 Peak intensity 0.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED J Series 5050B 6V K Class
 FWHM / FWTM 142.0° / 155.0°
 Efficiency 95 %
 Peak intensity 0.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED XHP35 HD
 FWHM / FWTM 157.0° / 171.0°
 Efficiency 93 %
 Peak intensity 0.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED XP-G2 HE
 FWHM / FWTM 150.0° / 161.0°
 Efficiency 93 %
 Peak intensity 0.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED XP-G3
 FWHM / FWTM 146.0° / 167.0°
 Efficiency 93 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED XP-G4
 FWHM / FWTM 140.0° / 148.0°
 Efficiency 96 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED PrevaLED Brick HP IP 2x6
 FWHM / FWTM 144.0° / 156.0°
 Efficiency 93 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED LUXEON 5050 Round LES
 FWHM / FWTM 143.0° / 156.0°
 Efficiency 92 %
 Peak intensity 0.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED LUXEON 5050 Round LES
 FWHM / FWTM 139.0° / 152.0°
 Efficiency 82 %
 Peak intensity 0.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

Protective plate, glass



LED LUXEON C
 FWHM / FWTM 150.0° / 168.0°
 Efficiency 91 %
 Peak intensity 0.3 cd/lm
 LEDs/each optic 4
 Light colour/type RGBW
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):





LED LUXEON HL2X-V
 FWHM / FWTM 148.0° / 157.0°
 Efficiency 95 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED SST-20 Gen2
 FWHM / FWTM 142.0 + 140.0° / 152.0 + 148.0°
 Efficiency 95 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED NV4WB35AM
 FWHM / FWTM 143.0° / 154.0°
 Efficiency 95 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED NVSxE21A
 FWHM / FWTM 136.0° / 145.0°
 Efficiency 93 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED OSCONIQ P 3030
 FWHM / FWTM 141.0° / 154.0°
 Efficiency 95 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED OSCONIQ P 3737 (3W version)
 FWHM / FWTM Asymmetric
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):

OSRAM
Opto Semiconductors


LED OSCONIQ P 3737 (3W version)
FWHM / FWTM Asymmetric
Efficiency 94 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

OSRAM
Opto Semiconductors


LED OSLOM Square CSSRM2/CSSRM3
FWHM / FWTM 143.0° / 155.0°
Efficiency 94 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

OSRAM
Opto Semiconductors

LED OSLOM Square CSSRM2/CSSRM3
FWHM / FWTM 142.0° / 156.0°
Efficiency 91 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):

OSRAM
Opto Semiconductors


LED OSLON SSL 150
FWHM / FWTM 145.0° / 157.0°
Efficiency 93 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

PHILIPS


LED Fortimo FastFlex LED 2x6 DPX G4
FWHM / FWTM 144.0° / 158.0°
Efficiency 89 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

SAMSUNG

LED LH351C
FWHM / FWTM Asymmetric
Efficiency 94 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):

SAMSUNG


LED LH351D
 FWHM / FWTM 156.0° / 164.0°
 Efficiency 94 %
 Peak intensity 0.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

SAMSUNG


LED LH502D
 FWHM / FWTM 144.0 + 142.0° / 158.0 + 156.0°
 Efficiency 95 %
 Peak intensity 0.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED Z5M1/Z5M2
 FWHM / FWTM 131.0° / 140.0°
 Efficiency 92 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:





Light distribution files

OPTICAL RESULTS (SIMULATED):




LED Z5M3-E1
 FWHM / FWTM 146.0 + 144.0° / 154.0 + 152.0°
 Efficiency 96 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files





LED Z5M4
 FWHM / FWTM 138.0° / 150.0°
 Efficiency 95 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED Z5M4-E1
 FWHM / FWTM 146.0 + 144.0° / 162.0 + 160.0°
 Efficiency 95 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

OPTICAL RESULTS (SIMULATED):



GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 7
FI-24100 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Poznan, Poland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)