

Standard Multilayer Ceramic Capacitors (Temperature compensating type)

UMK105CH820JV-F



■ Features

- Item Summary
50V, COH, 82pF, $\pm 5\%$, 0402
- Lifecycle Stage
Mass Production
- Standard packaging quantity (minimum)
Taping paper 10000pcs

■ Products characteristics table

| | |
|---------------------------------------|---|
| CaseSize (EIA/JIS) | 0402/1005 |
| Rated Voltage (max) | 50V |
| Capacitance | 82pF |
| Capacitance Tolerance | $\pm 5\%$ |
| Resistance | 10,000 M Ω min. |
| Q (min) | 1000 |
| Temperature Characteristics (EIA/JIS) | COH/CH |
| Temperature Range (EIA/JIS) | -55 to +125 $^{\circ}$ C/-55 to +125 $^{\circ}$ C |
| RoHS Compliance | Yes |
| Halogen Free | Yes |
| Soldering Method | Reflow |

■ External Dimensions

| | |
|---|-------------------|
| L | 1.0mm ± 0.05 |
| W | 0.5mm ± 0.05 |
| T | 0.5mm ± 0.05 |
| e | 0.25mm ± 0.10 |

2017.05.15

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.
 TAIYO YUDEN reserves the right to make change to the Date at any time without notice.
 Before making final selection, please check product specification.