


Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du Proprietaire.
Propriete de c FCI. Droits de reproduction FCI.







PERFORMANCE CHARACTERISTICS

CURRENT RATING: 1.5A AT 20°C (FULLY LOADED); 1 A AT 70°C (FULLY LOADED)

RATED VOLTAGE : 500 V AC (CONT /CONT)

OPERATING TEMPERATURE : -55°C TO 125°C


CONTACT RESISTANCE 20 MΩ MAX

INSERTION FORCE : 0.75N MAX/CONT

EXTRACTION FORCE : 0.15N MIN/CONT


INSULATION RESISTANCE : 10^4 MΩ MIN

NOTES 1.



2. THIS PRODUCT IS CSA APPROVED.
   THIS PRODUCT IS UL RECOGNIZED.
3. FOR RECOMMENDED PTH DIMENSIONS REFER DRAWING : BS.A.201572.001
4. THIS PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008

LAY-OUT
P.C.B.- HOLE



rev	ecn no	dr	date
A	CONVERSION REVISION 06	KN	14-09-01
B	DG05-0381	Kason	10-10-05
C	DG07-0362	Kason	05-09-07
D	DG10-0110	NZ	07-09-10

www.fciconnect.com

tolerance: 1DEC ±0.2 1DEC 2DEC ±0.1 2DEC ANGLES ±1° HOEKEN

projection | MM

Dr	N.OTTO	10-03-99	Product family	MILLIPICS	size A4 / Scale 3/1
Eng			Spec ref		
Chr			Material		ECN
Appr					

title: MPACS 8+2R RA RCP CONN TYPE D/ UPPER SHIELDING

dwg no: BS,C ,202260,014 | Rev. D

catalog no: HM2R87PA8108---- | CUMSTOMER | sheet 1 of 1

All rights strictly reserved.
Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

PDM: Rev:D STATUS:Released Printed: Mar 15, 2011

Downloaded from Arrow.com.