

## Han E High Temp male contact 0,75 mm<sup>2</sup>



Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Contacts
Series	Han E® High Temp
Type of contact	Crimp contact

### Version

Termination method	Crimp termination
Gender	Male
Contact identification	1 groove On the back crimp collar
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	0.75 mm <sup>2</sup>
Conductor cross-section [AWG]	AWG 18
Rated current	≤16 A
Contact resistance	≤1 mΩ
Stripping length	7.5 mm

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption

## Material properties

China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

## Commercial data

Packaging size	100
Net weight	1.29 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140052581
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522